


Accelerate the Development of Wireless Device Tests with Automated Test Development and Support

Quickly and easily meet time-to-market goals and reduce test cost

Agilent's Wireless Test Manager (WTM) software saves time and resources when automating mobile device testing. Designed for use with Agilent's 8960 Series wireless communication test set (E5515C/E) and E6621A PXT wireless communications test set the test manager makes test development, support, and use easier than ever. Applicable to manufacturing, R&D, and service, the test manager includes a test executive, technology-specific tests, easy-to-use interfaces, Visual Basic®.NET programming, and Windows® PC compatibility



Key Features

- Multi-format software platform (LTE FDD/TDD, W-CDMA, HSDPA, HSDPA, HSPA+, DC-HSDPA, cdma2000®, 1xEV-D0, IS-95, GSM, GPRS, EGPRS, IS-136 TDMA, AMPS, *Bluetooth*®, WLAN, and WiMAX™)
- Support Agilent 14565B device characterization software for battery drain testing
- Easy to customize test sequences, parameters, and specifications to meet your testing needs
- The power of Microsoft[®] Visual Basic .NET for custom test development (customer-provided development platform dependent upon WTM product selection)
- · Test wizard allows you to focus on test development by simplifying programming
- Agilent experience and measurement knowledge supplement your mobile phone design and testing expertise



Simplify and expedite test efforts

Designed specifically for test engineers, the test manager reduces the complexity associated with automating device testing. Why spend time on computer control and data management issues when the test manager does this for you and lets you focus on test?

Use Agilent or custom test plans

Run a pre-defined Agilent test plan, customize an existing plan, or create your own custom test plan. The test manager makes it easy to modify test parameters, adjust test limits, change the order of test steps, or build your own test plan—without programming.

Create custom test steps

To guide you through the process of adding your own custom test steps, the test manager features a test wizard. Tests created with the wizard and Visual Basic .NET are added to the test menu and can be used in a custom test plan without additional programming.

Flexibility to meet your test needs

The WTM makes it easy to configure system hardware. It provides for point and click set-up of the 8960 and E6621A test sets and selected power supplies, bar code readers, test fixtures, and printers. Other instruments can be added with a wizard using the development version. Plus, it gives you the flexibility to save test results for further analysis, and set run conditions to stop, continue, or retry on failure.

Reduce overall test costs

The WTM is easy to learn and simple to use. You will not have to learn complex applications and multiple programming languages to support test. Save on production line costs with the E6571E run-time license. The run-time license can be used with any technology covered by the WTM family. Use a standard WTM to develop a custom WTM application then deploy the custom application to your runtime system.

Wireless Test Manager products

Visual Basic .NET (USB security key)

- E6567E for LTE FDD/TDD, cdma2000, IS-95, AMPS, and 1xEV-D0 (development and runtime)
- E6568E for LTE FDD/TDD, W-CDMA, HSDPA, HSUPA, HSPA+, DC-HSDPA, GSM, GPRS, and EGPRS (development and run-time)
- E6569E suite (includes E6567E and E6568E)
- E6571E run-time only license combination and suite products
- N5880A Enhanced Wireless Test Manager for cdma2000, IS-95, and AMPS (development and run-time)
- N5882A Enhanced Wireless Test Manager for W-CDMA, HSDPA, HSUPA (development and run-time)
- N5884A Enhanced Wireless Test Manager for 1xEV-D0 (development and run-time)
- N4018C Bluetooth/WLAN Wireless Test Manager (run-time)
- N4019C Bluetooth/WLAN Wireless Test Manager (development and runtime)
- N6422C WiMAX Wireless Test Manager (development and run-time)
- N6423C WiMAX Wireless Test Manager (run-time)

Windows, Visual Basic .NET, and Microsoft are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other

cdma2000 is a registered certification mark of the Telecommunications Industry Association.

Bluetooth is a registered trademark of Bluetooth SIG, Inc., U.S.A. and licensed to Agilent Technologies, Inc.

WiMAX is a trademark of the WiMAX Forum.

www.agilent.com www.agilent.com/find/wtm

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	(11) 4197 3600
Mexico	01800 5064 800
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485	
China	800 810 0189	
Hong Kong	800 938 693	
India	1 800 112 929	
Japan	0120 (421) 345	
Korea	080 769 0800	
Malaysia	1 800 888 848	
Singapore	1 800 375 8100	
Taiwan	0800 047 866	
Other AP Countries(65) 375 8100		

Europe & Middle East

-aropo a maaro -	
Belgium	32 (0) 2 404 93 40
Denmark	45 45 80 12 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
United Kingdom	44 (0) 118 927 6201

For other unlisted countries: www.agilent.com/find/contactus

Revised: January 6, 2012

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2002-2008, 2011, 2012

Published in USA, August 13, 2012 5988-5833EN

