


Agilent N7502A Signal Simulation Systems

Configuration Guide

250 kHz to 20 GHz 250 kHz to 44 GHz

The N7502A signal simulation system is a complete signal generation and analysis system, with hardware and software combined to increase productivity and reduce setup time. The Agilent goal is to have your system up and running within hours of system delivery. The system incorporates the best of Agilent's expertise – both technical and practical – to ensure your system performance is optimized.

The N7502A configuration has significant flexibility so you can define a system most appropriate for your specific application needs. Use this guide to make the most informed selections and help build the system that gets your high performance signal generation job done right.





Configuration overview

Configuration of the N7502A system requires careful selection of the following parts:

- 1. Arbitrary waveform generator and supporting hardware
- 2. Microwave signal generator and modulation characteristics
- 3. Computer platform
- 4. System software components
- 5. Microwave spectrum analysis
- 6. Additional instruments (e.g., oscilloscope)
- 7. Physical layout, eg. benchtop or pre-configured in a system rack
- 8. Implementation and support services

The system offers configuration flexibility in each selection area, so that most applications can be addressed with the standard system. This configuration guide assists in identifying the required and optional features for the specific system you require.

In some cases, configurations may require additional unique or custom hardware or software, in addition to engineering services and program management for successful implementation. Please ask your local sales representative for more information.

Arbitrary waveform generator and supporting hardware

The N7502A includes the N6030A arbitrary waveform generator, with sampling rate of 1.25 GS/s and 15-bit resolution. With this wide bandwidth capability, the N6030A enables direct generation of IF waveforms with up to 500 MHz bandwidth from a single channel. Alternatively, the N6030A dual channels can be used as I/Q inputs of a microwave signal generator for signals with up to 1 GHz bandwidth.

Recommended Option:	○ N6030A-016	16 megasample memory
	• N6030A-500	18 slot PXI mainframe
Included:	• N6030A	arbitrary waveform generator

Microwave signal generator and modulation characteristics

The N7502A supports various sources and options. One or more sources can be configured in the system.

PSG vector signal generator

The E8267D PSG vector signal generator is normally the signal generator of choice, offering frequency coverage from 250 kHz to 20 GHz or 44 GHz. With the addition of the wideband I/Q modulation option, the E8267D offers 1 GHz modulation bandwidth above 3.2 GHz. Below 3.2 GHz, the I/Q modulation bandwidth is 160 MHz.

Recommended:	• E8267D	PSG vector signal generator
	• E8267D-015	1 GHz wide bandwidth I/Q modulation
Recommended options:	• E8267D-UNT	AM, FM, phase modulation and LF output
	• E8267D-UNR	Enhanced phase noise performance
	• E8267D-UNW	Narrow pulse modulation
	○ E8267D-420	Signal Studio for pulse building – enables advanced definition of pulsed waveform shaping and sequencing

E6432A VXI synthesizer

The E6432A VXI synthesizer is also a good choice for the N7502A. It covers the frequency range from 10 MHz to 20 GHz and offers I/Q modulation capability with I/Q modulation bandwidth of 40 MHz. The E6432A also offers direct IF upconversion of a 300 MHz IF, which can be generated by the N6030A on a single channel. The combination offers high quality upconversion with RF bandwidth of over 130 MHz from 300 MHz to 20 GHz. In addition, the E6432A offers increased switching speed compared with the PSG. Fully settled tuning between any two arbitrary frequencies across the entire frequency band requires less than 350 μs . Frequency switching to within 50 kHz of the desired frequency is typically 150 μs or less.

Optional source:	• E6432A	VXI microwave synthesizer, 10 MHz to 20 GHz
Recommended options:	E6432A-UNGE6432A-300	add I/Q modulator add IF upconversion
Choose VXI controller:	○ E8491B	IEEE1394 VXI Controller
Choose mainframe:	o N7502A-306	E1421B VXI mainframe 6 slot

Computer platform

Included:	○ N7502A-500	Tower PC to be used on a separate work surface outside the rack. This computer includes the following, or better: 3.40 GHz XEON processor, 2 GB SDRAM Memory, LAN, USB, and 19 inch flat panel display. The Windows XP® operating system is pre-installed.
Choose one:	○ N7502A-201	PXI embedded PC controller with LAN and GP-IB, for LAN connection to the workstation computer. Same as N6030A-501.
	○ N7502A-202	MXI-4 kit for 10 meter (copper) MXI connection to the workstation computer. This includes MXI-4 cards both in the PXI mainframe and in the workstation computer. Same as N6030A-502.
	○ N7502A-203	MXI-4 kit for 30 meter (fiber) MXI connection to the workstation computer. This includes MXI-4 cards both in the PXI mainframe and in the workstation computer.
	Note:	The N7502A-202 and -203 also include a GP-IB card in the PXI mainframe.

System software components

 $System\ software\ is\ pre\text{-}installed.$

Note: A demo copy of the software can be downloaded from the Agilent web site at www.agilent.com/find/signalsimulation.

Included:	○ N7509A	Waveform Generation Toolbox; powerful easy-to-use way to define and implement signal.
Choose one:	° N7502A-102	89601A vector signal analyzer software with 89601A-200, - 300, -AYA – provides vector signal analysis (VSA) capability, including from data taken by the oscilloscope
	 Baseband Studio for pulse building (PSG only) 	enables advanced definition of pulsed waveform shaping and sequencing.

Microwave spectrum analyzer

The PSA Series high-performance spectrum analyzer is recommended as a general-purpose tool for analyzing waveforms.

Recommended, Choose one:	• E4440A	PSA Series spectrum analyzer, 3 Hz to 26.5 GHz
	• E4448A	PSA Series spectrum analyzer, $3~\mathrm{Hz}$ to $50~\mathrm{GHz}$
Recommended options:	• E444XA-123	Switchable MW preselector bypass
	• E444XA-241	Flexible digital modulation analysis
	• E444XA-1DS	Internal Preamplifier
Choose one:	o E444XA-122	80 MHz bandwidth digitizer
	• E444XA-H70	70 MHz output

Additional instruments (e.g., oscilloscope)

Additional instruments can be added to the system as needed.

Oscilloscopes

The addition of a wide bandwidth oscilloscope enables the direct digitization of high frequency signals. This enables signals to be analyzed with up to 6 or 13 GHz bandwidth. Captured data can be analyzed using the scope or transferred to the computer for analysis by the VSA software.

Optional, choose one:	○ 54855A	Infiniium oscilloscope, 6 GHz, 4 channels, 20 GS/s per channel with 54855A-001 1 M MegaZoom memory/channel upgrade
	o DSO81304A	Infiniium oscilloscope, 13 GHz, 20/40 GS/s per channel

System racking

Agilent provides complete integration services for the N7502A, including racking, cabling, software loading, system test, documentation, and system warranty and support. A fully racked system ships to your site in a wooden crate. Users typically open the crate in a shipping area, then roll it on the built-in wheels to the facility where the system will be used, plug it in and begin running it. The instruments are already positioned in the rack for optimized performance, while meeting strict ergonomics and safety requirements. This is the best way to get up and running quickly and ensure that the startup process goes smoothly.

Recommended, Choose one:	N7502A-601	1.2 m rack, 110 V power, display not rack mounted
C	N7502A-602	$1.2~\mathrm{m}$ rack, $220~\mathrm{V}$ power, display not rack mounted
C	N7502A-603	$1.6\ \mathrm{m}$ rack, $110\ \mathrm{V}$ power, display not rack mounted
c	N7502A-604	1.6 m rack, 220 V power, display not rack mounted

Alternatively, users can specify the system without racking, eg. for benchtop setups. In this case, the instruments typically arrive together in a single shipment, but each instrument is in an individual box. The user unpacks the instruments one by one, positions them in a suitable location on a benchtop, typically stacking instruments as needed. Users then must follow instructions to ensure proper cabling and interconnections of instruments. Users must then plan for appropriate ergonomics and safety for their specific setup.

Implementation and support services

Warranty Information

The N7502A is supported with a one-year return-to-Agilent warranty. Upon request, Agilent can quote extensions to three-year warranty and also three-year calibration. Agilent also offers services to assist in integration, training, consulting, repair, and calibration. Please contact your Agilent sales representative for more information.

Application Assistance

Agilent's signal generation and analysis experts are available to help you take full advantage of the system for your unique application. User training and consulting can help you get up to speed quickly. If your application has unique requirements, Agilent program managers and engineering professionals can help define and implement unique functionality.

They ensure that your custom requirements are successfully implemented, from initial design through acceptance.

Related Agilent Literature

• N7502A Signal Simulation System

Product overview 5989-1827EN

• N6030A Arbitrary Waveform Generator

Technical overview 5989-1457EN

• E8267D PSG Vector Signal Generator

Data sheet 5989-0697EN

• Infiniium Oscilloscopes and

89601A Vector Signal Analysis Software

Data sheet 5989-0947EN

Ordering Information

Contact your Agilent representative.

Web Resources

For additional product information, visit www.agilent.com/find/signalsimulation

Agilent Technologies' Test and Measurement Support, Services, and Assistance

Agilent Technologies aims to maximize the value you receive, while minimizing your risk and problems. We strive to ensure that you get the test and measurement capabilities you paid for and obtain the support you need. Our extensive support resources and services can help you choose the right Agilent products for your applications and apply them successfully. Every instrument and system we sell has a global warranty. Support is available for at least five years beyond the production life of the product. Two concepts underlie Agilent's overall support policy: "Our Promise" and "Your Advantage."

Our Promise

Our Promise means your Agilent test and measurement equipment will meet its advertised performance and functionality. When you are choosing new equipment, we will help you with product information, including realistic performance specifications and practical recommendations from experienced test engineers. When you receive your new Agilent equipment, we can help verify that it works properly and help with initial product operation.

Your Advantage

Your Advantage means that Agilent offers a wide range of additional expert test and measurement services, which you can purchase according to your unique technical and business needs. Solve problems efficiently and gain a competitive edge by contracting with us for calibration, extra-cost upgrades, out-of-warranty repairs, and onsite education and training, as well as design, system integration, project management, and other professional engineering services. Experienced Agilent engineers and technicians worldwide can help you maximize your productivity, optimize the return on investment of your Agilent instruments and systems, and obtain dependable measurement accuracy for the life of those products.



www.agilent.com/find/emailupdates

Get the latest information on the products and applications you select.

For more assistance with your test and measurement needs or to find your local Agilent office go to: www.agilent.com/find/assist For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Phone or Fax

United States:

(tel) 800 829 4444 (fax) 800 829 4433

Canada:

(tel) 877 894 4414 (fax) 905 282 6495

China:

(tel) 800 810 0189 (fax) 800 820 2816

Europe:

(tel) 31 20 547 2111

Japan:

(tel) (81) 426 56 7832 (fax) (81) 426 56 7840

Korea:

(tel) (080) 769 0800 (fax) (080) 769 0900

Latin America:

(tel) (305) 269 7500

Taiwan:

(tel) 0800 047 866 (fax) 0800 286 331

Other Asia Pacific Countries:

(tel) (65) 6375 8100 (fax) (65) 6755 0042 Email: tm_ap@agilent.com

Product specifications and descriptions in this document subject to change without notice.

Windows is a U.S. registered trademark of Microsoft Corporation.

© Agilent Technologies, Inc. 2005 Printed in USA, May 27, 2005 5989-2914EN

