

Hardware Supported

Test instruments

- E6621A PXT wireless communications test set
- N6051A LTE RF parametric test with test mode signaling
- E5515E mainframe (or equivalent E5515C/B/T with Options 002 and 003)
- E1987A fast switching mobile test application (revision A.14.14 or later)
- E1963A W-CDMA mobile test application (revision A.19.14 or later)
- E6703H W-CDMA lab application (revision H.01.14 or later)
- E6785H fast switching lab application (revision H.01.15 or later)
- E6703H W-CDMA lab application (revision H.01.14 or later)
- E6785H fast switching lab application (revision H.01.15 or later)
- E1968A GSM/GPRS/EGPRS mobile test application (revision A.07.21 or later)
- Agilent 66311B, 66319B, and 66321B power supplies
- Agilent 34970 with 34901A, 34903A, and 34907A data acquisition/switch unit

Fixtures

- Tescom TC-5941, TC-5942, and TC-5952B

Adapters

- Agilent 82357A USB/GPIB interface
- National Instruments GPIB-USB to GPIB

PC Cards

- Agilent GPIB
- National Instruments GPIB
- Advantech PCI 1750 digital I/O
- Control RocketPort 95870-3 and 99096-3 multi-port serial

Peripherals

- Symbol LS-1220-1200A fixed bar code reader
- Symbol LS-3603MX-1200A, P300FZY, and LS4004I-I100 handheld bar code reader
- HP printers
- Epson TM-U200D and TM-U220D strip printer

PC requirements

- Operating system: Microsoft® Windows® 7 Professional and Enterprise
- Microsoft Visual Studio®.NET (for development)
- Microsoft Internet Explorer version 5.0 or later
- 600 MHz Pentium III or higher
- 256 MB RAM minimum (512 MB is recommended for normal development)
- 200 MB free hard drive space
- CD-ROM
- GPIB card or converter with VISA drivers (one per test system)
- USB port for security key connection
- Serial ports for fixtures, device control, and bar code reader

Order Information

- E6568E 2G/3G/LTE Wireless Test Manager
- Option 100 development and run-time license with software
- Option 200 development and run-time software upgrade (upgrades to the latest E6568E version)

For More Information

- E6568E Wireless Test Manager specifications and product literature are available at www.agilent.com/find/e6568e
- 8960 Series 10 test set specifications, product literature, application notes, and configuration guide are available at www.agilent.com/find/8960

Agilent
Advantage
Services



Agilent Advantage Services is committed to your success throughout your equipment's lifetime.

www.agilent.com/find/advantageservices

Agilent Electronic Measurement Group
DEKRA Certified
ISO 9001:2008
Quality Management System

www.agilent.com/quality



Agilent Email Updates

www.agilent.com/find/emailupdates
Get the latest information on the products and applications you select.

www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Microsoft, Windows, and Visual Studio are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries.

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2005-2007, 2011, 2012

Published in USA, August 21, 2012
5989-3073EN



Agilent Technologies