



Agilent N2X  
**Next-Generation  
Ethernet Interfaces**

10/100/1000BASE-T and 1000BASE-X (SFP)  
XP-2, XR-2 and XS-2 Test Cards  
N5550B, N5551B, N5552B, N5553B, N5630B  
Technical Data Sheet



**Next generation Ethernet test cards designed to increase scalability and reduce test cost with its high port density and new CPU per port architecture that enables multiple users to share ports on a card.**

## Key Features

- **Flexible hardware to match your test needs**
- **Industry's highest protocol performance**
- **Industry's highest protocol scalability**
- **Full control over all traffic generation parameters**
- **Comprehensive API & Open-Library of Automated Test Scripts**

## Product Overview

The Agilent N2X is the industry's most comprehensive test solution for testing the development and deployment of network services for converging network infrastructures. Service providers, network equipment manufacturers (NEMs), and component manufacturers can verify service attributes of entire networks end-to-end, while also isolating problems down to individual networking devices and subsystems. Agilent N2X delivers unparalleled test realism to verify the ultimate performance, scalability and resilience of carrier grade services and infrastructure.

The Agilent N2X Next Generation Ethernet Test Cards are available with 10/100/1000 BASE T and 1000 BASE-X interfaces including dual mode RJ-45/SFP. In conjunction with N2X Packets & Protocols Application they provide multi-port traffic generation, scalable protocol emulation and unprecedented performance analysis of today's Ethernet networks and devices. From wire-speed traffic generation and analysis to full emulation of Internet-scale routing topologies using the latest protocols and technologies, Agilent provides the most flexible, comprehensive and easy to use system available today.

These next generation Ethernet test cards are designed to increase test coverage and reduce test cost. Each port has a dedicated CPU and RAM – no sharing of CPUs and no compromise in performance. Next generation Ethernet Test Cards support an individual user per port. Multiple users can concurrently utilize their own test port maximizing the use of test equipment and return on year investment.

The foundation of all N2X test cards is a powerful yet flexible traffic generation engine capable of verifying everything from L2 Ethernet Switches through to multi-chassis carrier class routing nodes and networks. The real time traffic generator with multi-profile traffic scheduler and thousands of streams, programmable field modifiers and industry leading test payload provides unparalleled test realism and flexibility to ensure you can generate the traffic to meet any test scenario. Combined with comprehensive, real-time layer 1 through to 4 transmit and receive statistics and graphs including packet loss, latency and misordering N2X is able to verify the data-plane functionality, performance and scalability of your device or network.

Agilent N2X's traffic generator and receiver capabilities are tightly coupled with powerful protocol emulation hardware on all XR-2 and XS-2 test cards. This integration will ensure your devices are tested under the most realistic environment possible and remove the need to manually configure traffic addresses when completing performance measurements. N2X provides emulation of the most popular routing protocols, including BGP, OSPF, ISIS and RIP and the latest MPLS protocols, including RSVP-TE, LDP/CR-LDP, L2oMPLS (Martini), and VPLS. Multicast protocols can be verified easily with our IGMP and PIM-SM protocol emulations. Access networks and devices can be tested with PPPoX and DHCP protocols.

All N2X next generation Ethernet test cards provide the data capture memory required to enable detailed analysis from a single test session. N2X allows users to set a range of triggers including a specific event threshold as a 'trigger' to initiate or halt capture. Combined with powerful capture analysis software, users can quickly isolate, analyze and debug performance issues.

Agilent N2X test cards offer superior test flexibility and investment protection. Built upon powerful programmable logic technology test functionality can be continually adapted to ever-changing standards and evolving technologies.

#### Flexible Hardware options to meet your test needs

Along with flexibility in interface types, N2X next generation Ethernet test cards are available in three key performance variants designed to match your specific test needs:

- **XP-2** – offered as a four port only card, this cost effective packet generation and analysis test card provides users with full access to N2X’s easy to use Packets application. It’s unique PDU builder and flexible packet generator lets you manipulate and define the contents of all protocol fields quickly and easily. Large numbers of streams and the industries most comprehensive test payload enables users to simulate realistic traffic mixes and accurately verify the forwarding performance and QoS capabilities of your system under test.
- **XR-2** – offered in both 2 and four port variants, this card offers seamless integration of traffic and protocol testing for realistic testing of Internet routers and switches. Combined with the N2X Packets and Protocols application these cards validate leading-edge services such as Multicast VPNs and IPTV on network devices. It can emulate multiple protocols simultaneously, creating sophisticated network topologies required to verify that the device can concurrently manage numerous protocol engines and routing tables while continuously forwarding traffic.
- **XS-2** – offered as a 2 port only variant, this test card provides the protocol scalability and performance needed to test the highest performing Internet routers and switches. It sets a new benchmark for protocol scalability and performance testing with the ability to emulate the largest multi-protocol topologies of any test equipment on the market.

	2 Port	4 Port
<b>XP-2</b>	N/A	N5553B -10/100/1000 BASE-T, 1000 BASE-X (SFP)
<b>XR-2</b>	N5552B -10/100/1000 BASE-T, 1000 BASE-X (SFP)	N5550B -10/100 BASE-T N5551B -10/100/1000 BASE-T, 1000 BASE-X (SFP)
<b>XS-2</b>	N5630B -10/100/1000 BASE-T, 1000 BASE-X (SFP)	N/A

Figure 1 : Next generation Ethernet available hardware combinations

### Industry's Highest Protocol Performance

A high performance CPU with on-board cache enables the industry's fastest protocol engine.

When testing high performance routers, a key measurement is to determine the convergence time. A router has "converged" when it has learned all routes from its peers.

The XS-2 next generation Ethernet test card is the only card that available today that can determine the convergence time of routers by advertising routes faster than any other test equipment.

### Industry's Highest Protocol Scalability

1 GB of RAM per port enables the industry's highest protocol scalability.

A key measurement is to determine the number of routing peers that a router can support. For example, Layer 3 VPNs require each core and edge router to support a BGP-4 session. Any router must support thousands of BGP-4 peering sessions.

The XS-2 next generation Ethernet test card is the only card that available today that can practically measure the absolute scalability of routers. Multiple XS-2 test cards can be added into a single test system, to increase the scalability of the entire system – the possibilities for scalability testing are nearly endless.

For scalability testing, the N5630B is significantly more economical than buying multiple test cards. Taking the cost of test interfaces and router ports into account, the N5630B halves the cost of test by concentrating more processing power on a single card.

### Full Control over ALL Traffic Generation Parameters

Agilent N2X's innovative "flexible PDU builder" technology delivers the most advanced solution for traffic generation and analysis available. Any type of data-plane frame or packet can be generated, including custom formats. Users can manipulate and define the contents of all protocol fields quickly and easily. You no longer have to wait for industry standards, or write unique test scripts to test new and proprietary protocol encapsulations.

### Comprehensive API & Open-Library of Automated Test Scripts

N2X's automated QuickTests, based on Agilent's Journal of Internet Test Methodologies, make it easy to perform even the most complex tests. N2X's powerful API makes it easy to customize scripts to match your specific test needs.

In addition, proprietary scripts can be created using the Tcl/Tk scripting environment. With only a few lines of code, powerful test scenarios can be executed with precision.

## Configuration and Ordering Details

### Ethernet test card variants

- N5550B : 4-port 10/100 BASE-T XR-2 Test Card.
- N5551B : 4-port 10/100/1000 BASE-T 1000BASE-X (SFP) Ethernet XR-2 Test Card.
- N5630B : 2-port 10/100/1000 BASE-T 1000BASE-X (SFP) Ethernet XS-2 Test Card.

### Discontinued ethernet test card variants

- N5552B : 2-port 10/100/1000 BASE-T 1000BASE-X (SFP) Ethernet XR-2 Test Card. (This product is discontinued)
- N5553B : 4-port 10/100/1000 BASE-T 1000BASE-X (SFP) Ethernet XP-2 Test Card. (This product is discontinued)

### Pluggable SFP optics options

- Option 001: Include one - 1000Base SX SFP (850nm)
- Option 002: Include one - 1000Base LX SFP (1310nm)
- Option 003: Include one - 1000Base ZX SFP (1550nm)
- Not applicable for N5550B.

## Software Compatibility

The E7880B Packets License enables the traffic generation and analysis features on the XP-2, XR-2 & XS-2 test cards. XR-2 and XS-2 cards can take advantage the multi-protocol emulation environment plus integrated traffic & routing features available in the E7881B Packets & Protocols license.

The N5550B, N5551B, N5552B, N5553B and N5630B test cards require version N2X Packets and Protocols Release 6.8 or later.

## Technical Specifications

### Physical layer specifications

#### Connectivity

Port Density & connection type	<ul style="list-style-type: none"> <li>N5550B: 4 - 10/100 RJ-45 electrical Ethernet ports</li> <li>N5551B: 4 - 10/100/1000 RJ-45 electrical and SFP Ethernet ports</li> <li>N5552B: 2 - 10/100/1000 RJ-45 electrical and SFP Ethernet ports</li> <li>N5553B: 4 - 10/100/1000 RJ-45 electrical and SFP Ethernet ports</li> <li>N5630B 2 – 10/100/1000 RJ-45 electrical and SFP Ethernet ports</li> </ul>
Connection Type	<ul style="list-style-type: none"> <li>Supports SFP (SFF-8074i v1.0)</li> <li>RJ-45 (tri-rate)</li> <li>Auto-detect of MDI/MDI-X and auto-configure</li> </ul>

#### Interface Operation Modes

Terminal	<ul style="list-style-type: none"> <li>Normal operation – transmit and receive interfaces operate independently</li> </ul>
Transmit loop-back	<ul style="list-style-type: none"> <li>Transmitted data is electrically looped back to the receive interface. The optical receive interface is disabled in this mode. (SFP interface only)</li> </ul>
Monitor	<ul style="list-style-type: none"> <li>Received data is looped back to the transmit interface. Received data is also copied into the test port where all real time Rx measurements are made. Capture and subsequent analysis are also fully functional in this mode (SFP interface only)</li> </ul>

#### Transmit Clock Sources

Clock source	<ul style="list-style-type: none"> <li>Internally generated based on chassis system reference</li> </ul>
--------------	--

#### Front Panel Indicators

Ethernet Indicators (for each optical and electrical interface)	<ul style="list-style-type: none"> <li><b>Link:</b> Green - Ethernet framing is detected on the receive interface and link has been established with a link partner.</li> <li><b>Activity:</b> Green - Data is transmitted or received</li> </ul>
---	---

### Alarms and Errors

Real-Time Alarm Detection	<ul style="list-style-type: none"> <li>Current module status is indicated on the user interface and front panel LEDs</li> <li>Alarm events are reported in a trace log during the measurement interval</li> <li>Number of errored seconds is reported per alarm type (count of 1s intervals in which the alarm is detected at least once)</li> </ul>
---------------------------	--

#### Error monitoring

- For the selected Ethernet statistics the following parameters are recorded:
  - Number of individual occurrences of the event
  - Number of seconds during which at least one event occurred
- Statistics are User selectable, dependant on the application. These may include, but are not limited to, the following: Frames transmitted, Valid frames received, Octets transmitted, Octets received, Runts, Short events, Jumbo frames, Jabbers, FCS errored frames, ARP frames, Flow control frames, VLAN tagged frames.

### Link layer specifications

#### Auto-negotiation

The Test Card supports auto-negotiation. This may be disabled independently on each port.

#### PAUSE Frames

The Test Card can generate, count and respond to PAUSE frames.

#### Measurement System

Measurements are synchronized across all cards within the test system.

Result types	<ul style="list-style-type: none"> <li>Cumulative:           <ul style="list-style-type: none"> <li>Measurements are reported from the start of the measurement interval</li> </ul> </li> <li>Sampled:           <ul style="list-style-type: none"> <li>Measurements are reported from the most recently completed sampling interval</li> </ul> </li> <li>Measurement Interval           <ul style="list-style-type: none"> <li>1 second to 7 days</li> </ul> </li> <li>Sampling Interval           <ul style="list-style-type: none"> <li>1 second to 1 hour</li> </ul> </li> <li>Measurement clock:           <ul style="list-style-type: none"> <li>20 ns resolution +/-0.5 ppm/year clock drift</li> </ul> </li> <li>3 ppm max. difference between systems</li> </ul>
--------------	---

## Real-time Statistics

Unless otherwise specified all statistics are on a per port basis.

### Glossary

Short event	<ul style="list-style-type: none"> <li>A sequence of bytes of insufficient length to form a valid Ethernet frame (&lt;18 bytes)</li> </ul>
Runt	<ul style="list-style-type: none"> <li>A frame with less than 64 bytes (excluding preamble) and a valid FCS.</li> </ul>
Long frame	<ul style="list-style-type: none"> <li>A frame longer than 1522 bytes (or 9022 for jumbo frames) with a valid FCS.</li> </ul>
Jumbo frame	<ul style="list-style-type: none"> <li>A frame between 1519 and 9022 bytes with a valid FCS and an Ethertype of 0x8870.</li> </ul>
Jabber frame	<ul style="list-style-type: none"> <li>A frame longer than 1522 bytes (or 9022 for jumbo frames) with an invalid FCS.</li> </ul>
Pattern Match	<ul style="list-style-type: none"> <li>Count of frames matching specified fields in the header</li> </ul>
PPIC (Packet Payload Integrity Check).	<ul style="list-style-type: none"> <li>The PPIC field contains a 16-bit CRC calculated over the "protected payload". The "protected payload" refers to any of the following: IP packet payload (default) MPLS frame payload L2 frame payload User-defined</li> </ul>

### General Statistics

Per Port Stats	<ul style="list-style-type: none"> <li>Tx and Rx % line use</li> <li>Misdirected packets</li> <li>Error rate</li> </ul>
Per Stream Stats.	<ul style="list-style-type: none"> <li>Rx and Tx stream packets and octets</li> <li>Misordered packets</li> </ul>
Per Stream & Port Stats.	<ul style="list-style-type: none"> <li>Tx and Rx test packets and octets</li> <li>Expected Rx packets</li> <li>Throughput</li> <li>Packets not received</li> <li>Average latency</li> <li>Minimum/maximum latency</li> <li>PPIC violations (ie. Count on payload error)</li> </ul>
Ethernet	<ul style="list-style-type: none"> <li>Tx and Rx frame and Octet counts</li> <li>Tx and Rx Throughput</li> <li>Tx and Rx MAC control frames</li> <li>Short events received</li> <li>Runt frames received</li> <li>Tx &amp; Rx long frames</li> <li>Jabber frames received</li> <li>Tx &amp; Rx invalid FCS frames</li> </ul>
VLAN	<ul style="list-style-type: none"> <li>Tagged Tx and Rx frame and Octet counts</li> </ul>
MPLS	<ul style="list-style-type: none"> <li>Tx and Rx packets</li> </ul>
IPv4	<ul style="list-style-type: none"> <li>Tx and Rx packet and octet counts</li> <li>Header checksum errors</li> <li>Fragmented packet count</li> <li>Throughput</li> </ul>

IPv6

- Tx and Rx packet and octet counts
- Throughput counts

User Defined Statistics

- Powerful features allow statistics collection on a per stream, per-MPLS tag, per-VLAN tag or other user-defined-index basis

### Card Specific Specifications

All measurements are per physical interface port.

Capture RAM	All models: 27MB		
CPU RAM	N5550B, N553B: 128MB N5551B, N5552B: 256MB N5630B: 1GB		
	All XS-2 and XR-2	All XP-2	
Maximum number of stream groups	8192	1023	
Maximum number of traffic streams	32,768	32,768	
Maximum number of field inserters	24,576	128	
Minimum transmit layer 2 frame length (bytes)	5	5	
Maximum transmit layer 2 frame length (bytes)	65,534	65,534	
Maximum receive layer 2 frame length	1000 BASE-X	65,535	65,535
frame length	1000 BASE-T	65,535	65,535
	100 BASE-T	16,000	16,000
	10 BASE-T	13,000	13,000

### Applicable Standards

PCS/MAC	<ul style="list-style-type: none"> <li>IEEE 802.3</li> </ul>
Address Resolution Protocol	<ul style="list-style-type: none"> <li>IETF RFC 826 An Ethernet Address Resolution Protocol</li> </ul>
IP IEEE 802 Networks	<ul style="list-style-type: none"> <li>IETF RFC 1042</li> </ul>

## Mechanical Specifications

Physical	<ul style="list-style-type: none"> <li>• Width 206 mm</li> <li>• Depth 313 mm</li> <li>• Height 31.0 mm</li> <li>• Weight 1.5 kg</li> </ul>
Electrical	<ul style="list-style-type: none"> <li>• Power consumption 50W</li> </ul>

## Environmental

Operating temperature	• 5 °C to 40 °C
Storage temperature	• -40 °C to 70 °C
Maximum Relative Humidity	• Maximum relative humidity 80% for temperatures up to 31 °C, decreasing lineally to 50% relative humidity at 40 °C (non-condensing).

## Regulatory Compliance

Electrical (Electromagnetic Compliance - EMC)	<ul style="list-style-type: none"> <li>• As per IEC 61326-1:1997 + A1:1998 / EN 61326-1:1997 + A1:1998</li> </ul> <p>Electrical equipment for measurement, control and laboratory use (Class A)</p> <ul style="list-style-type: none"> <li>• EMC Directive 89/336/EEC (including 93/68/EEC)</li> <li>• For complete compliance information refer to Declaration of Conformity E7900-91300 (Tested for regulatory compliance with Agilent Technologies SFPs)</li> </ul>
Electrical (Safety)	<ul style="list-style-type: none"> <li>• Safety requirements for electrical equipment for measurement, control, and laboratory use</li> <li>• Low voltage directive 73/23/EEC</li> </ul>
Optical (Safety)	<ul style="list-style-type: none"> <li>• Complies with IEC 60825 Class 1, and CDRH 21 CFR 1040 - Class I Laser Products when equipped with Agilent supplied SFP optical transceivers</li> </ul>

## Application Programming Interface

An Application Programming Interface (API) is provided through the Tool command Language (Tcl). The API is intended to automate configuration tasks, create repeatable test sequences, or to integrate the test system into a larger test system. The scripting language is Tcl/Tk. Tcl/Tk comes bundled with the E7880A Traffic Generation and Analysis software.

An API client may run directly on the N2X System Controller, or may run on any other PC or UNIX workstation connected to the System Controller via a TCP/IP connection. API clients communicate with the System Controller via an included package of Tcl commands. All functions available through the GUI are available via the API. Any changes made through the API are automatically reflected on the GUI.

## Discontinued

The following products have been discontinued.

- N5552B : 2-port 10/100/1000 BASE-T 1000BASE-X (SFP) Ethernet XR-2 Test Card
- N5553B : 4-port 10/100/1000 BASE-T 1000BASE-X (SFP) Ethernet XP-2 Test Card

## Agilent N2X

Agilent's N2X multi-service tester combines leading-edge services with carrier grade infrastructure testing and emulation. The N2X solution set allows network equipment manufacturers and service providers to more comprehensively test new services end-to-end, resulting in higher quality of service and lower network operating costs.

## Software and Support Agreement

To protect your investment in the Agilent N2X, every new system includes an initial 12-month comprehensive system-based warranty and Software and Support Agreement (SSA).

Renewing Agilent support services ensures uninterrupted technical support and software upgrades, giving you confidence in N2X throughout the life of your system.

The N2X technical support portion of your SSA includes assistance with product operation and measurements, and verification that the N2X equipment is in correct working order.

## Warranty and Support

### Hardware Warranty

All N2X hardware is warranted against defects in materials and workmanship for a period of 1 year from the date of shipment.

### Software Warranty

All N2X software is warranted for a period of 90 days. The applications are warranted to execute and install properly from the media provided.

This warranty only covers physical defects in the media, whereby the media is replaced at no charge during the warranty period.

## Ordering Information

To order and configure the test system, consult your local Agilent field engineer.

## Sales, Service and Support

N2X must be serviced by an approved Agilent Technologies service centre, please contact us for more information.

### United States:

Agilent Technologies  
Test and Measurement Call Center  
P.O. Box 4026  
Englewood, CO 80155-4026

1-800-829-4444

### Canada:

Agilent Technologies Canada Inc.  
2660 Matheson Blvd. E  
Mississauga, Ontario  
L4W 5M2  
1-877-894-4414

### Europe:

Agilent Technologies  
European Marketing Organisation  
P.O. Box 999  
1180 AZ Amstelveen  
The Netherlands  
(31 20) 547-2323

### United Kingdom

07004 666666

### Japan:

Agilent Technologies Japan Ltd.  
Measurement Assistance Center  
9-1, Takakura-Cho, Hachioji-Shi,  
Tokyo 192-8510, Japan  
Tel: (81) 426-56-7832  
Fax: (81) 426-56-7840

### Latin America:

Agilent Technologies  
Latin American Region Headquarters  
5200 Blue Lagoon Drive, Suite #950  
Miami, Florida 33126  
U.S.A.  
Tel: (305) 269-7500  
Fax: (305) 267-4286

### Asia Pacific:

Agilent Technologies  
19/F, Cityplaza One, 1111 King's Road,  
Taikoo Shing, Hong Kong, SAR  
Tel: (852) 3197-7777  
Fax: (852) 2506-9233

### Australia/New Zealand:

Agilent Technologies Australia Pty Ltd  
347 Burwood Highway  
Forest Hill, Victoria 3131  
Tel: 1-800-629-485 (Australia)  
Fax: (61-3) 9272-0749  
Tel: 0-800-738-378 (New Zealand)  
Fax: (64-4) 802-6881

This information is subject to change without notice.  
Printed on recycled paper

© Agilent Technologies, Inc. 2009  
Printed in USA August 12, 2009  
5989-4586EN

