



This document is no longer available.

To view and download the original
DesignCon paper, go to:

[http://www.home.agilent.com/upload/cmc_upload/
All/DesignCon2008_Performance_DUT.pdf](http://www.home.agilent.com/upload/cmc_upload/All/DesignCon2008_Performance_DUT.pdf)



Agilent Technologies

www.agilent.com

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2008
Printed in USA, November 5, 2008
5989-8861EN



Agilent Technologies