

Agilent EEsof EDA

ANADIGICS Relies on Agilent's ADS for RFICs Design - a Customer Success Story

This document is owned by Agilent Technologies, but is no longer kept current and may contain obsolete or inaccurate references. We regret any inconvenience this may cause. For the latest information on Agilent's line of EEsof electronic design automation (EDA) products and services, please go to:

www.agilent.com/find/eesof





ANADIGICS Relies on Agilent EEsof Advanced Design System for Design of RFICs

Customer Success story



"Our decision to use ADS as an exclusive RF front-end design tool has paid off in a big way. It has allowed ANADIGICS to focus on what we do best – develop RFIC products".

Shihab Al-Kuran Director of Design Technology Engineering ANADIGICS, Inc.

Customer: ANADIGICS, Inc. (www.anadigics.com)

Challenge: To optimize the use of design tools for maximum productivity

Solution: Standardize on Agilent EEsof's Advanced Design System

Results:

- Several first-time design successes – including a new 40 Gb/s preamplifier for wireline applications.
- Engineering productivity improvements

The Company

ANADIGICS is a leading worldwide supplier of radio frequency integrated circuit (RFIC) solutions for growing broadband and wireless communications markets. The company's innovative high frequency RFICs enable manufacturers of communications equipment to enhance overall system

performance by reducing the size and weight of their products, increasing power efficiency, improving reliability, and reducing manufacturing cost and time to market.

The Challenge

RFIC technology is moving fast and being pushed to its limit by tougher requirements on size, performance, and power. In order to remain a leader in this market. ANADIGICS knew they needed to optimize the design productivity tool-set used by the engineers. They realized that they were not being effective supporting five different CAD tools as well as an internal spice tool. "Trying to keep all the different tools and models up to date was a nightmare," explains Shihab Al-Kuran, Director of Design Technology Engineering. "We were fragmented with all of these different tools and it was going to require more resources to support it well."

The Solution

ANADIGICS made a bold decision to switch from using several different design tools to just one front-end RF design tool. They standardized on Agilent EEsof Advanced Design System software and models.

"Agilent is not just a pure software company. It has RF designers, fabrication facilities, and a modeling group. Agilent understands what we are trying to do because they do it themselves," said Al-Kuran. "This was a big factor in choosing to work with Agilent."

To make the transition easier, ANADIGICS formed a relationship with Agilent EEsof in which they became involved in the early development of the Advance Design System. "We were able to get early access to cutting edge technology for our designs as well as provide feedback to the ADS





tool designers. This arrangement became beneficial for both companies", said Al-Kuran.

One example of accessing cutting edge design technology is a project that ANADIGICS has contracted with the Solution Services Group inside Agilent EEsof. "We have co-developed an advanced solution that allows us to have a more efficient design flow for RFIC integration," explained Al-Kuran. "The project directly links Momentum RF with ADS circuits by allowing circuit and EM co-simulation and co-optimization. This results in faster simulation, with more accurate results. all in the same user interface. We have seen a dramatic reduction in the development time of circuits that require intense EM simulation."

The Results

"Our decision to use ADS as an exclusive RF front-end design tool has paid off in a big way", exclaimed Al-Kuran. "It has allowed ANADIGICS to focus on what we do best – develop RFIC products".

Often, RF design tends to be viewed as black magic. ANADIGICS credits their ability to reduce the number of design iterations with the many features in ADS as well as its ability to improve the IC design flow.

"There are several areas where we have achieved first time design success using ADS. That is very uncommon", said Al-Kuran. One example is a Microwave DC/DC converter circuit where the measured results

matched perfectly with the simulation results. The converter was quickly incorporated into over 80% of ANADIGICS' datacom fiber optic products because of the high degree of confidence they had in the part.

Another first time design success is a new 40 Gb/s fiber optic pre-amplifier. "This was a very challenging design that required the use of almost every simulation technology in ADS", said Al-Kuran. The Convolution Simulator was used to analyze high frequency effects such as dispersion, a capability that is not typically found in standard Spice simulators. The EM tools were used for package modeling and signal integrity for these high data rates. "We are very excited about the results."

Engineering productivity has improved using ADS because tools like Momentum, EM simulation, are built-in. "Our engineers use Momentum to simulate passive matching circuits in the same environment as the active circuitry. They don't have to spend time transferring designs from one tool to another, nor do they need to learn several tools", said Al-Kuran.

The sensitivity analysis capability in ADS has also been an important feature for ANADIGICS' designers. It has enabled them to center a design by adjusting component values to improve the predicted manufacturing yield. Designers can then translate the sensitivity analysis results into

component specifications required from vendors.

"ADS has reduced our design cycle by months. In these economic times, this saves us hundreds of thousands of dollars in cost and more importantly brings in millions in revenue by being early to market", said Al-Kuran.

For more information about ANADIGICS, go to: www.anadigics.com

For more information about Agilent EEsof EDA and Advanced Design System, visit our Website: www.agilent.com/eesof-eda

For more information about other Agilent test and measurement products, go to:
www.agilent.com/find/tmdir

© Copyright 2001 Agilent Technologies Data is subject to change Printed in the USA 5/01





For more information about Agilent EEsof EDA, visit:

www.agilent.com/find/eesof



www.agilent.com/find/emailupdates Get the latest information on the products and applications you select.



www.agilent.com/find/agilentdirect Quickly choose and use your test equipment solutions with confidence.

www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas	
Canada	(877) 894-4414
Latin America	305 269 7500
United States	(800) 829-4444

Asia Pacific	
Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866

1 800 226 008

Europe & Middle East

Thailand

Austria	0820 87 44 11	
Belgium	32 (0) 2 404 93 40	
Denmark	45 70 13 15 15	
Finland	358 (0) 10 855 2100	
France	0825 010 700*	
	*0.125 €/minute	
Germany	01805 24 6333**	
	**0.14 €/minute	
Ireland	1890 924 204	
Israel	972-3-9288-504/544	
Italy	39 02 92 60 8484	
Netherlands	31 (0) 20 547 2111	
Spain	34 (91) 631 3300	
Sweden	0200-88 22 55	
Switzerland	0800 80 53 53	
United Kingdom	44 (0) 118 9276201	
Other European Countries:		
www.agilent.com/find/contactus		

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2008 Printed in USA, June 28, 2001 5989-9996EN

Revised: March 27, 2008

