

Agilent X-Series Signal Analyzers (MXA/EXA) Single Acquisition Combined Fixed WiMAX™ Measurement Application (N9074A-XFP)

Technical Overview

The Agilent N9074A-XFP single acquisition combined Fixed WiMAX measurement application is a breakthrough, high-speed manufacturing test solution available as an option on Agilent's highest speed mid-range, general-purpose X-Series signal analyzers – the MXA (N9020A) and EXA (N9010A).

Measurement	Measurement Item	Result
-----TX Power-----		
Burst1	Total Power	-7.268 dBm
	Peak PSD	-15.709 dBm/MHz
Burst2	Total Power	-7.267 dBm
	Peak PSD	-15.708 dBm/MHz
Burst3	Total Power	-7.268 dBm
	Peak PSD	-15.709 dBm/MHz
-----TX Output Spectrum-----		
Burst1	-----Reference Channel-----	
	Total Power	-7.268 dBm
	Peak PSD	-15.709 dBm/MHz
	-----Negative Offset A-----	
	Min Margin Level	-86.750 dBm
	Min Margin from Limit Line	-39.846 dB
	Minimum margin offset frequency	-3.776 MHz
	Pass/Fail	Pass
	-----Positive Offset A-----	
	Min Margin Level	-87.429 dBm
	Min Margin from Limit Line	-38.252 dB
	Minimum margin offset frequency	3.800 MHz
	Pass/Fail	Pass
	-----Negative Offset B-----	
	Min Margin Level	-81.807 dBm
	Min Margin from Limit Line	25.201 dB

Example of combined Fixed WiMAX measurement result

Features and Benefits

- Supports IEEE standard 802.16d (802.16-2004)
- Supports demodulation of uplink and downlink signals using IEEE 802.16-2004 modulation formats including BPSK, QPSK, 16QAM and 64QAM
- SCPI¹-based measurement application allows production familiar remote programming commands for ease-of-test software development
- Flexible selections of predefined parameters allow easy and customizable set-up of the measurements to suit various production test requirements
- Varied measurement methods to meet different needs for best speed or best accuracy
- Supports frequency hopping for broadband and multi-frequency points measurements
- Tabular user interface showing the parameter, measurement, and result lists for easy viewing
- Parameter list view displays SCPI commands, related parameter name and value in one table and is easier to understand than only showing a list of SCPI commands
- Additional RF envelope view provides troubleshooting tool for the time alignment between target signal and the instrument

1. SCPI is the abbreviation for Standard Commands for Programmable Instruments.



Agilent Technologies

Introduction

The increasing complexity of today's mobile devices, driven by the need for multi-frequency/band coverage, support of multiple formats (2G/3G and emerging communication technologies) and multiple applications (phone, multimedia and PDA) combined with ever-increasing pressure to achieve lower cost factors are driving manufacturers to look for ways to reduce test times and test costs for these complex devices. By using general-purpose RF test equipment without any call-processing for production testing, it is possible to apply new measurement processing techniques to drastically reduce the test time required and keep test costs well under control.

The single acquisition combined Fixed WiMAX measurement application allows manufacturers to make measurements much faster than traditional measurements. In the combined measurement applications a single acquisition of data is used for multiple measurements, saving valuable time in comparison to traditional measurements that recapture data for each individual measurement. The N9074A-XFP option is a SCPI-based measurement application with varied parameter setups and a simple user interface. It supports multiple measurements for different signals including frequency hopping signal. The N9074A-XFP option is designed for time-critical tests on the production line, and the high dynamic range of the Agilent signal analyzers ensures that the measurements remain as accurate as possible.

Single acquisition: contains one continuous block of captured data using predefined capture settings. The capture period can be defined by test engineers to suit the requirements for specific device tests, for example, how many bursts are required to provide enough data to ensure a good measurement on the DUT.

Combined measurements: imply that the measurement sequences performed by the analyzer can accommodate transmitter power measurements and any mix of transmitter output spectrum modulation accuracy measurements performed on the data collected within the capture period.

Advantages of the combined Fixed WiMAX application measurements

Acceleration of test speed without required measurement switching and using fewer acquisitions

Compared with traditional one-button measurements, which limit the "speed" of tests due to measurement switching time (such as from SEM to EVM), the combined Fixed WiMAX measurement application uses SCPI-based programming to configure the X-Series signal analyzer to conduct the specified measurements ahead of time, without measurement switching, and with fewer acquisitions that normally would require processing of the data after each capture is completed.




Figure 1. Combined Fixed WiMAX measurement

In order to perform the single acquisition combined measurements, the N9074A-XFP measurement application option requires option B25 to be installed on either the N9020A MXA or N9010A EXA signal analyzer.

Available measurements:


- Transmit Power
- Transmit Output Spectrum
- Modulation Accuracy

Measurement overview

The N9074A–XFP combined Fixed WiMAX measurement application is ideal for characterizing the overall PHY layer performance of a Fixed WiMAX signal. Take advantage of standardized tests to evaluate a transmitter against the IEEE standard for manufacturing test.

The N9074A–XFP combined Fixed WiMAX measurement application provides all of the IEEE 802.16d Fixed WiMAX transmitter tests. Through SCPI commands, turn Transmit Output Spectrum measurement and Modulation Accuracy measurement On or Off to assure complete assessment or perform only a few tests to reduce overall test time and speed device evaluation.

The Transmit Power measurement specifies the total power of the transmitted signal, and the power spectral density is also provided.



The screenshot displays the Agilent N9074A software interface for a Combined Fixed WiMAX measurement. The main window shows a table of measurement results for three bursts. The table has three columns: Measurement, Measurement Item, and Result. The results are as follows:

Measurement	Measurement Item	Result
-----TX Power-----	Total Power	-7.258 dBm
Burst1	Peak PSD	-16.709 dBm/MHz
	Total Power	-7.257 dBm
Burst2	Peak PSD	-15.708 dBm/MHz
	Total Power	-7.268 dBm
Burst3	Peak PSD	-16.709 dBm/MHz
	Total Power	-7.268 dBm
	Peak PSD	-16.709 dBm/MHz

The interface also shows various settings and controls on the right side, including a 'ViewDisplay' menu with options for 'Display', 'RF Envelope', 'Result List', and 'Param List'. The status bar at the bottom indicates 'MSG' and 'STATUS'.

Figure 2. Transmit Power measurement

Transmit Output Spectrum measures spurious signal levels for up to four (A/B/C/D) pairs of offsets. The specification called out in the standard is used as the default, however, the profile of the test masks can be changed as required by using related SCPI commands. The Pass/Fail sign indicates the result status for each offset.




Figure 3. Transmit Output Spectrum measurement

Modulation Accuracy measurement provides the results of Frequency Error, Symbol Error, RMS EVM in dB, RMS EVM in percent, I/Q Offset, Absolute Spectrum Flatness Minimum Margin, Absolute Spectrum Flatness Minimum Margin Pass/Fail flag, Difference Spectrum Flatness Minimum Margin, and Difference Spectrum Flatness Minimum Margin Pass/Fail flag. Figure 4 shows an example of Modulation Accuracy measurement.




Figure 4. Modulation Accuracy measurement

The N9074A–XFP combined Fixed WiMAX measurement application performs capture according to the capture setup, and after the capture is completed, the acquired data is calculated. The burst setup can be modified for different captures, parameters, and measurements by using SCPI commands. If it is a frequency hopping signal, multiple frequencies in the Center Freq of Burst Setup can be specified and the “Suffix”, which is the time interval for frequency or attenuation change needed by the RF front end, should be designated in the capture setup. There are three types of measurement methods – Best Speed, Balanced, and Best Accuracy to meet specific priorities.

Greater flexibility of measurement setup

The N9074A-XFP measurement application option provides high flexibility for the setup of combined measurement parameters. Figure 5 shows an example of a parameter list view. Parameter name, with its SCPI command and value, is listed in this view. The list is ordered in SCPI commands and identifying what parameter corresponds to a specific command can be easily found. The value can be verified or modified in three ways – sending SCPI commands, using the menu and front panel keys, or using a mouse and keyboard. This is more convenient than having to access the SCPI programming interface for minor changes.

Name	SCPI	Value
EVM Threshold Lower	:CALCulate:CFWimax:EVM:BURSt:THReshold:LOWer	List:Amplitude[36]
EVM Threshold Upper	:CALCulate:CFWimax:EVM:BURSt:THReshold:UPPer	List:Amplitude[36]
Abs Spectral Flatness Lower Limit	:CALCulate:CFWimax:EVM:LiMit:SPECTrum:AMPFlatness:ABSolute:LOWer	List:Amplitude[2]
Abs Spectral Flatness Upper Limit	:CALCulate:CFWimax:EVM:LiMit:SPECTrum:AMPFlatness:ABSolute:UPPer	List:Amplitude[2]
Diff Spectral Flatness Lower Limit	:CALCulate:CFWimax:EVM:LiMit:SPECTrum:AMPFlatness:DIFFerential:LOWer	0.10 dB
Diff Spectral Flatness Upper Limit	:CALCulate:CFWimax:EVM:LiMit:SPECTrum:AMPFlatness:DIFFerential:UPPer	0.10 dB
Tx Output Spectrum Limit Level	:CALCulate:CFWimax:TOSPECTrum:LiMit:DATA	List:Amplitude[4]
View Selection	:DISPlay:CFWimax:VIEW:SELEct	PARAMeter
X Auto Scaling	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:X:SCALe:COUPle	On
X Scale Div	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:X:SCALe:PDIVision	400.0 ps
X Ref Value	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:X:SCALe:RLEVEl	0.000 s
X Ref Position	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:X:SCALe:RPOSiTion	Left
Y Auto Scaling	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:Y:SCALe:COUPle	Off
Y Scale Div	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:Y:SCALe:PDIVision	10.00 dB
Y Ref Level	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:Y:SCALe:RLEVEl	10.00 dBm
Y Ref Position	:DISPlay:CFWimax:VIEW1:WiNDow1:TRACe:Y:SCALe:RPOSiTion	Top
Arrival Time Uncertainty	:SENSe:CFWimax:CAPTure:ATUNcertain	0.000 s
Burst Attenuation	:SENSe:CFWimax:CAPTure:BURSt:ATtenuation	List:Amplitude[36]
Burst Frequency	:SENSe:CFWimax:CAPTure:BURSt:FREQuency	List:Frequency[36]
Gate Source	:SENSe:CFWimax:CAPTure:BURSt:GATE:SOURce	List:Enum[36]
Burst Length	:SENSe:CFWimax:CAPTure:BURSt:LOAD	List:Time[36]
Burst Number	:SENSe:CFWimax:CAPTure:BURSt:NUMBer	2
Burst Prefix	:SENSe:CFWimax:CAPTure:BURSt:PREFix	List:Time[36]
Burst Suffix	:SENSe:CFWimax:CAPTure:BURSt:SUFFix	List:Time[36]
Burst Type	:SENSe:CFWimax:CAPTure:BURSt:TYPE	DYNAMIC
Capture Offset	:SENSe:CFWimax:CAPTure:OFFSet	0.000 s
Mod Accuracy Start Burst	:SENSe:CFWimax:EVM:BURSt:STARt	1
Mod Accuracy Stop Burst	:SENSe:CFWimax:EVM:BURSt:STOP	2
Mod Accuracy Modulation Format	:SENSe:CFWimax:EVM:DEMod	AUTO
Mod Accuracy Enable	:SENSe:CFWimax:EVM:ENABle	On

Figure 5. Parameter List view

Simplified user interface for reduced processing overhead allows for highest speed

The user interface of the N9074A-XFP measurement application option is designed for maximum efficiency. All of the results listed in the Result List view can be queried by SCPI commands (see Figures 2, 3, and 4).

Comprehensive user interface for troubleshooting

For troubleshooting or diagnostic purposes, the N9074A-XFP measurement application option provides a graphical user interface that displays measurement traces. The RF Envelope view is useful for setting time alignment between target signal and the instrument. Figure 6 shows a view of an RF envelope. In this view, the instrument acquires a trace with two bursts for demodulation. The RF Envelope view can be turned off during the measurement for higher speed.




Figure 6. RF Envelope view

Key Specifications

N9074A-XFP single acquisition combined Fixed WiMAX measurement application		
Description	N9020A MXA	N9010A EXA
Transmit power		
Absolute power accuracy 20 to 30 °C	±1.29 dB	±1.46 dB
Spectrum emission mask		
10 MHz Integration BW RBW = 100 kHz 5.05 MHz offset Accuracy		
Relative	±0.63 dB	±0.63 dB
Absolute 20 to 30 °C	±1.37 dB	±1.55 dB
Description	Specifications	Supplemental information
64QAM EVM		
EVM		
Operating range	0.1 to 8%	0.1 to 8%
Floor	-48 dB (0.37%)	-45 dB (0.57%)
Accuracy		
from 0.5% to 2%	±0.20%	±0.30%
from 2% to 8%	±0.10%	±0.10%

Ordering Information

Below you will find information on how to order your X-Series signal analyzer with the single acquisition combined Fixed WiMAX measurement application.

For further information, refer to the *MXA Configuration Guide*, literature number 5989-4943EN or the *EXA Configuration Guide*, literature number 5989-6531EN.

Instruments	Model number	Options
<i>Required options</i>		
MXA signal analyzer	N9020A	503 or 508 or 513 or 526 – frequency range up to 26.5 GHz
EXA signal analyzer	N9010A	503 or 507 or 513 or 526 – frequency range up to 26.5 GHz
MXA or EXA signal analyzer	N9020A or N9010A	B25 25 MHz analysis bandwidth
Single acquisition combined Fixed WiMAX measurement application	N9074A	XFP
<i>Recommended options</i>		
MXA signal analyzer	N9020A	P03 or P08 or P13 or P26 for MXA – Preamplicator up to 26.5 GHz
EXA signal analyzer	N9010A	P03 for EXA – Preamplicator up to 3.6 GHz
MXA or EXA signal analyzer	N9020A or N9010A	EA3 – Electronic attenuator (3.6 GHz)
EXA signal analyzer	N9010A	PC2 dual core processor (standard on MXA)

Literature Resources

Literature title	Number
Agilent MXA Signal Analyzers	
<i>Brochure</i>	5989-5047EN
<i>Data Sheet</i>	5989-4942EN
<i>Configuration Guide</i>	5989-4943EN
<i>Option BBA: Analog Baseband IQ Inputs Technical Overview</i>	5989-6538EN
Agilent EXA Signal Analyzers	
<i>Brochure</i>	5989-6527EN
<i>Data Sheet</i>	5989-6529EN
<i>Configuration Guide</i>	5989-6531EN
Agilent X-Series Signal Analyzers (MXA/EXA)	
<i>Demonstration Guide</i>	5989-6126EN
<i>X-Series Signal Analyzer Measurement Application Overview</i>	5989-8019EN
<i>EMI Precompliance Measurements Using MXA/EXA</i>	5990-3690EN
<i>Analog Demodulation Measurement Application Technical Overview</i>	5989-6535EN
<i>Noise Figure Measurement Application Technical Overview</i>	5989-6536EN
<i>Phase Noise Measurement Application Technical Overview</i>	5989-5354EN
<i>Pulse Measurement Software Technical Overview</i>	5990-3801EN
<i>W-CDMA, HSDPA/HSUPA Measurement Application Technical Overview</i>	5989-5352EN
<i>802.16 OFDMA Measurement Application Technical Overview</i>	5989-5353EN
<i>GSM/EDGE Measurement Application Technical Overview</i>	5989-6532EN
<i>EDGE Evolution Measurement Application Flyer</i>	5989-9837EN
<i>cdma2000®, 1xEV-DO Measurement Application Technical Overview</i>	5989-6533EN
<i>TD-SCDMA Measurement Application Technical Overview</i>	5989-6534EN
<i>LTE Measurement Application Technical Overview</i>	5989-6537EN
<i>Single Acquisition Combined WLAN Measurement Application Technical Overview</i>	5990-3519EN
<i>Single Acquisition Combined Fixed WiMAX® Measurement Application Technical Overview</i>	5990-3520EN
<i>DVB-T/H Measurement Application Technical Overview</i>	5990-3569EN
<i>DTMB Measurement Application Technical Overview</i>	5990-3570EN
<i>Remote Language Compatibility Technical Overview</i>	5989-6539EN
<i>Speed Enhancement and Removable Hard Drive</i>	5989-6541EN
<i>Using Agilent X-Series Analyzers (MXA/EXA) for Measuring and Troubleshooting Digitally Modulated Signals</i>	5989-4944EN
<i>Using Agilent X-Series Analyzers (MXA/EXA) Preselector Tuning for Amplitude Accuracy in Microwave Spectrum Analysis</i>	5989-4946EN
<i>Maximizing Measurement Speed with Agilent X-Series Signal Analyzers (MXA/EXA)</i>	5989-4947EN
<i>Making Precompliance Measurements with Option EMC on X-Series Analyzers (MXA/EXA)</i>	5990-3133EN
Agilent VXA Vector Signal Analyzer Measurement Applications	
<i>VXA Vector Signal Analyzer Measurement Application, Technical Overview</i>	5989-7463EN
<i>Option AYA Vector Modulation Analysis, Technical Overview</i>	5989-7464EN
<i>Option B7R WLAN Modulation Analysis, Technical Overview</i>	5989-7465EN



Agilent Email Updates

www.agilent.com/find/emailupdates
Get the latest information on the products and applications you select.



Agilent Direct

www.agilent.com/find/agilentdirect
Quickly choose and use your test equipment solutions with confidence.



www.agilent.com/find/open
Agilent Open simplifies the process of connecting and programming test systems to help engineers design, validate and manufacture electronic products. Agilent offers open connectivity for a broad range of system-ready instruments, open industry software, PC-standard I/O and global support, which are combined to more easily integrate test system development.



www.lxistandard.org
LXI is the LAN-based successor to GPIB, providing faster, more efficient connectivity. Agilent is a founding member of the LXI consortium.

cdma2000 is a registered certification mark of the Telecommunications Industry Association. Used under license.

WiMAX is a trademark of the WiMAX Forum.

Remove all doubt

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment throughout its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements. For information regarding self maintenance of this product, please contact your Agilent office.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance, onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to:

www.agilent.com/find/removealldoubt

Product specifications and descriptions in this document subject to change without notice.

www.agilent.com

www.agilent.com/find/N9074A

www.agilent.com/find/N9074A_XFP

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

Canada	(877) 894-4414
Latin America	305 269 7500
United States	(800) 829-4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Thailand	1 800 226 008

Europe & Middle East

Austria	01 36027 71571
Belgium	32 (0) 2 404 93 40
Denmark	45 70 13 15 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	07031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
Switzerland	0800 80 53 53
United Kingdom	44 (0) 118 9276201

Other European Countries:

www.agilent.com/find/contactus

Revised: October 6, 2008

© Agilent Technologies, Inc. 2009
Printed in USA, March 23, 2009
5990-3520EN



Agilent Technologies