
Agilent E8663D PSG RF Analog Signal Generator

Configuration Guide





This guide assists in the ordering process for the E8663D PSG RF analog signal generator.



Standard product includes installation guide, electronic documentation set (CD-ROM), adapters, and country specific power cord.

Agilent PSG RF Analog Signal Generator Options

Step 1. Choose a frequency range (required)

Ordering number	Description	Purpose
E8663D-503	Frequency range from 100 kHz to 3.2 GHz	Selects the maximum frequency of the signal generator
E8663D-509	Frequency range from 100 kHz to 9.0 GHz	Selects the maximum frequency of the signal generator

Step 2. Choose order convenience bundle

Ordering number	Description	Purpose	Requires
E8663D-063	E8663B backwards compatibility option bundle - 1EU, 1E1, 1EH, UNX, UNT	Provides all the same options included in the E8663B	

Step 3. Choose modulation

Ordering number	Description	Purpose	Requires
Standard	CW and pulse modulation	Generates continuous wave (CW) signals and pulse modulation (150 ns minimum pulse width)	
E8663D-UNT	AM, FM, phase modulation, and LF output	Adds analog modulated signals	
E8663D-UNW	Narrow pulse modulation	Generates pulse modulated signals (20 ns minimum pulse width)	
E8663D-1SM ¹	Scan modulation	Provides deep AM modulation	E8663D-UNT

Step 4. Choose attenuator

Ordering number	Description	Purpose
Standard	No step attenuator	Generates signals with output power levels ranging from -20 dBm to maximum power
E8663D-1E1	Step attenuator	Generates signals with output power levels ranging from -135 dBm to the maximum power

Step 5. Choose high output power

Ordering number	Description	Purpose
Standard	Standard output power	Generates maximum RF output power of +15 dBm
E8663D-1EU	High output power	Generates maximum RF output power of +21 dBM

^{1.} E8663D-1SM is not compatible with E8663D-1EM (rear panel connectors).

Step 6. Choose spectral purity

Ordering number	Description	Purpose
Standard	Standard spectral purity	Provides low phase noise
E8663D-UNX ¹	Ultra-low phase noise performance	Improves phase noise performance close-to-carrier
E8663D-UNY ¹	Enhanced ultra-low phase noise	Improves phase noise for carrier offsets from 1 Hz to 300 kHz
E8663D-1EH	Improved harmonics below 2 GHz	Improves harmonic performance for carrier frequencies < 2 GHz

Step 7. Choose ramp sweep

Ordering number	Description	Purpose
E8663D-007	Analog ramp sweep	Generates fully synthesized ramp (analog) sweep

Step 8. Choose instrument security

Ordering number	Description	Purpose
E8663D-008	Removable flash memory	Provides 8 GB of removable compact flash memory; all user-accessible files are located on this memory card

Step 9. Choose custom options ²

Custom options add unique capabilities to the signal generator for specific applications.

Ordering number	Description	Purpose	Requires
E8663D-H1S	Provides 1 GHz IN and OUT on rear panel to improve phase noise	Enables use of an external frequency reference to improve spectral purity	E8663D-UNX or E8663D-UNY

Step 10. Choose instrument accessories and connector

Ordering number	Description	Purpose
Standard with every E8663D	Type-N (f) RF output connector	Type-N (m) to 3.5 mm (f) adapter is included
E8663D-1CM	Rack mount flange kit	Provides flange kit to mount the signal generator into a standard EIA 19" rack
E8663D-1CN	Front handle kit	Provides front handles for carrying instrument (not for rack mount)
E8663D-1CP	Rackmount kit with front handles	Provides flange handles and a flange to mount the signal generator into a standard EIA 19" rack
E8663D-1CR	Rack slide kit	Provides a non-tilting rack slide kit
E8663B-1EM ³	Moves all front panel connectors to the rear panel	Simplifies cable management in rack mount environments

^{1.} E8663D-UNX and E8663D-UNY are mutually exclusive. Choose one or the other or neither.

^{2.} All specified performance attributes of custom options are tested at 25 ° C (± 3 ° C) unless otherwise noted. For more information, contact Agilent Technologies.

^{3.} Not compatible with Option 1SM (scan modulation).

Step 11. Choose documentation

Ordering number	Description
E8663D-CD1	CD-ROM containing the English documentation set
E8663D-ABA	Printed copy of the English documentation set
E8663D-0BW	Printed copy of the E8663D assembly-level service guide

Step 12. Choose a warranty plan

Ordering number	Description
Included	Warranty Assurance Plan, Return to Agilent, 3 years, standard
R-51B-001-5C	Warranty Assurance Plan, Return to Agilent, 5 years

Step 13. Choose a calibration plan

Ordering number	Description
E8663D-UK6	Commercial calibration certificate and test data
E8663D-A6J	ANSI Z540-1-1994 calibration
E8663D-AMG	Agilent Cal + Uncertainties + Guardbanding (accredited cal)
R-50C-011-3	Calibration Assurance Plan, Return-to-Agilent, 3 years
R-50C-011-5	Calibration Assurance Plan, Return-to-Agilent, 5 years
R-50C-016-3	Agilent Calibration + Uncertainties + Guardbanding, 3 years
R-50C-016-5	Agilent Calibration + Uncertainties + Guardbanding, 5 years
R-50C-021-3	ANSI Z540-1-1994 Calibration, 3 years
R-50C-021-5	ANSI Z540-1-1994 Calibration, 5 years

Step 14. Choose start-up assistance options

Ordering number	Description
PS-S10	Remote scheduled assistance 1-999 hours
PS-S20	Start-up assistance
PS-T10-ASG	Signal generator and source basics; 0.5 day (H7215B-165), max. 8 students on site
PS-X10	Custom services to be qualified by Agilent

Upgradeable Options

For complete upgrade details, including firmware, visit: www.agilent.com/find/E8663D_upgrade_table

Customer-installable and service center-installable upgrade kits are available for the E8663D PSG signal generator. If an option is not mentioned that you would like to have upgraded on your PSG, please contact your local Agilent representative about our customized upgradeable options.

Ordering number	Description	Upgrade Contents	Additional requirements	Incompatible with
E8663DU-UNW	Narrow pulse modulation	License key	None	None
E8663DU-1EU	High output power	License key	None	None
E8663DU-007	Analog ramp sweep	License key	None	None
E8663DU-008	Removable flash memory	License key and hardware	None	None
E8663DU-1EH	Improved harmonics below 2 GHz	License key	None	None
E8663DU-UNT	AM, FM, phase modulation, and LF output	License key	None	None
E8663DU-1E1	Adds a step attenuator to provide calibrated minimum output power levels of -135 dBm while maintaining superior level accuracy	License key and hardware	None	None
E8663DU-R2C	Core instrument firmware enhancements	License key	None	None
E8663DU-UNX	Adds ultra-low phase noise performance	License key and hardware	None	None
E8663DU-UNY ¹	Adds enhanced ultra-low phase noise performance	License key and hardware	S/N ≥ 5042	S/N < 5042
E8663DU-2NY ²	Adds enhanced ultra-low phase noise performance	License key and hardware	S/N < 5042	S/N ≥ 5042

^{1.} Agilent service center installation only.

Web Resources

For additional product information, visit: www.agilent.com/find/psg

For information about renting, leasing or financing Agilent's latest technology, visit: www.agilent.com/find/buyalternatives

For accessory information, visit: www.agilent.com/find/accessories

Related Agilent Literature

Agilent PSG Microwave Signal Generators Brochure, Literature number 5989-1324EN

E8257D PSG Microwave Analog Signal Generator Data Sheet, Literature number 5989-0698EN Configuration Guide, Literature number 5989-1325EN

E8267D PSG Microwave Vector Signal Generator Data Sheet, Literature number 5989-0697EN Configuration Guide, Literature number 5989-1326EN

E8663D PSG RF Analog Signal Generator Data Sheet, Literature number 5990-4136EN

^{2.} Agilent factory installation only. Requires an additional factory installation and calibration charge (E8663DU-700).



myAgilent

www.agilent.com/find/myagilent

A personalized view into the information most relevant to you.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Agilent is a founding member of the LXI consortium.





www.agilent.com/find/ThreeYearWarranty

Beyond product specification, changing the ownership experience.

Agilent is the only test and measurement company that offers three-year warranty on all instruments, worldwide



Agilent Assurance Plans

www.Agilent.com/find/AssurancePlans

Five years of protection and no budgetary surprises to ensure your instruments are operating to specifications and you can continually rely on accurate measurements.



www.agilent.com/quality

Agilent Electronic Measurement Group DEKRA Certified ISO 9001:2008 Quality Management System

Agilent Channel Partners

www.agilent.com/find/channelpartners

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.

www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at: www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	(11) 4197 3600
Mexico	01800 5064 800
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 375 8100

Europe & Middle East

Belgium	32 (0) 2 404 93 40
Denmark	45 45 80 12 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
United Kingdom	44 (0) 118 927 6201

For other unlisted countries:

www.agilent.com/find/contactus

RP-09-27-13

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2013 Published in USA, November 25, 2013 5990-4137EN

