
# **Agilent M9216A**

PXI High Voltage Data Acquisition Module



**Data Sheet** 

32-Channel, 250 kS/s, 16-bit, 5 V/100 V



### OVFRVIFW



### Introduction

The Agilent M9216A is a multi-channel, large-range voltage measurement unit capable of acquiring dynamic positive voltage levels from multiple channels simultaneously, making it ideal for automated test equipment (ATE) in automotive electronics applications.

### **Product description**

The M9216A is a two slot, PXI-based, high voltage data acquisition module with a 16-bit resolution that allows simultaneous measurement of 8 channels of positive voltages ranging from 1 mV to 100 V. Each channel in the module comes with a concurrent 5 V and 100 V measurement range instead of having multiple switchable voltage ranges. This allows each channel to acquire signals that fluctuate between very low and very high voltage levels without the need for switching ranges and doing separate measurements.

The M9216A module also comes with a built-in 32 to eight multiplexer, enabling 32 measurement ports to be connected to the eight acquisition channels expanding it to a full blown 32 channel acquisition module. Alternatively, these channels can also be routed out via auxiliary output connector J101 eliminating the need for external multiplexers and pin matrix cards for additional measurements.

With the support of up to 32 channels with each channel equipped with dual concurrent measurement ranges, the M9216A module is capable of doing fast parallel voltage level measurements with guaranteed accuracy. This is ideal for the automotive industry and since most automotive applications do not require negative voltage measurements, the M9216A's 16-bit ADC is fully used for positive voltages giving it better resolution hence better accuracy.

# **Application**

Automotive

### **Features**

- 16-bit resolution
- 32 channels
- · Dual concurrent voltage ranges for each channel:
  - $\circ$  > 5 V (1 mV to 5 V)
  - $\circ$  > 100 V (20 mV to 100 V)
  - Input accuracy at 5 V
  - > zero offset : 5 V range 200 uV, 100 V range 1 mV
  - > gain (% of reading): 5 V range 0.05%,
     100 V range 0.05%
  - $^{\circ}~>$  noise @ 3 sigma: 5 V range 200 uV, 100 V range 2 mV
- Auxiliary outputs for additional measurements
- Connector compatibility with cPCI, PXI-H, PXI-1
- · Included drivers: IVI-COM, IVI-C, LabVIEW G

#### **Customer values**

- High-channel count for fast and accurate acquisition of multiple voltage levels and doing parallel testing
- Concurrent dual range for each channel to support large voltage range without the need for switching ranges
- Auxiliary output for additional measurements



# EASY SETUP, TEST, AND MAINTENANCE

### Hardware platform

#### Compliance

The M9216A data acquisition module is PXI compliant, using either a cPCI, PXI-1 or PXI Hybrid slot. The product can be integrated with other test and automation modules in cPCI, PXI-1 and PXI-H chassis (hybrid slots). The PXI format offers high performance in a small, rugged package. It is an ideal deployment platform for many automated test systems. A wide array of complementary PXI products is currently available. Products include multimeters, waveform generators, local oscillators, digitizers, down converters and switch multiplexers.

#### Input range

The M9216A comes with a large input range with dual concurrent measurement range of 5 V and 100 V for each channel. The 5 V range caters for voltage levels of 1 mV to 5 V while the 100 V range caters for voltage levels of 20 mV to 100 V, enabling every channel to acquire voltage levels ranging from 1 mV to 100 V without the need for switching ranges, making it ideal for fast measurement needs.

### Measurement channels & auxiliary outputs

The built-in 32 to eight multiplexer is constructed where each dual range acquisition channel in the M9216A is connected to four ports through a 4-to-1 multiplexer, two of the ports can also be routed out via the auxiliary output connector J101. Every eight ports connect to a one of four floating commons making it one acquisition bank as shown in Figure 1, making a total of four acquisition banks.

### Software platform

#### 10 libraries

Agilent IO Libraries Suite offers FAST and EASY connection to instruments and the newest version extends that capability to include modular instruments.

NEW support for PXI — The Agilent IO Libraries Suite helps you display ALL of the modules in your system. From here you can view information about the installed software or start the modules' soft front panel. Launch the modules' soft front panel directly from Agilent Connection Expert. Drivers

The M9216A high voltage data acquisition module is supplied with a comprehensive portfolio of module drivers, documentation, examples, and software tools to help you quickly develop test systems with your software platform of choice. The module comes with IVI-COM, IVI-C, and LabVIEW G software drivers that work in the most popular test and measurement development environments including LabVIEW and LabWindows/CVI from National Instruments, Microsoft® C/C++, C#, and VB.NET®

### Easy software integration

The module software support provides context sensitive help, complete documentation and code examples that allow a quick module set up and basic acquisition functionalities. These code examples can be easily modified, so that the card can be quickly integrated into a test system. Included are application code examples for LabVIEW, LabWindows/CVI, Visual Studio<sup>®</sup> C, C++, and C# and Visual Basic.




Figure 1. Example of a data acquisition bank (Bank 1)

# TECHNICAL SPECIFICATIONS

Voltage input input (general)	
Number of Channels	8 concurrent dual range channels
Resolution	16 bit
Sampling rate	250 kS/s
Analog bandwidth (anti-aliasing filter)	85 kHz
Dual range specifications	
5 V 100 V	1 mV to 5V 20 mV to 100 V
Input coupling	DC
Input impedance	550 kΩ (typical)
Internal sample memory	30,000 samples for 5 V and 100 V range per channel (multiple mode)
	240,000 samples for 5 V and 100 V range for one channel (single mode)
Trigger	Software and digital trigger
	Pre and post trigger sample acquisition
	Timed delay
Voltage input input accuracy (at 25 + 3° C)	
5 V Range	
Zero offset	±200 μV
Gain (% of reading)	±0.05%
Noise 3 sigma	200 μV
100 V Range	
Zero offset	1 mV
Gain (% of reading)	0.05%
Noise 3 sigma	2 mV
Multiplexer	
Input channels	32
Output channels	8 channels to ADC
	8 channels to primary auxiliary out
	8 channels to complementary auxiliary out
Maximum input voltage	100 V
Maximum input current	0.5 A 45 V
Maximum common return pin voltage with respect to chassis ground	45 V
Power	
Maximum current consumption from PXI	0.0.4
5 V 3.3 V	0.8 A 0.5 A
Maximum input voltage	100 V
Maximum input voitage  Maximum input current	0.5 A
Maximum common return pin voltage with respect to chassis ground	45 V
Warm up time	0.5 hour
·	

NOTE: A minimum system warm up time of 15 minutes is required. For optimum accuracy, a warm up time of one hour is recommended.

# GENERAL SPECIFICATIONS

Environmental and physical	
Operating temperature	0 to 55° C
Storage temperature	–20° C to 70° C
Relative humidity	0% to 80% non condensing
Dimensions	3U, 2-slot, PXI/cPCI module; 40.30 mm x 129.11 mm $\times$ 212.73 mm (1.59 in. $\times$ 5.08 in. $\times$ 8.38 in.)
Weight	0.51 kg (1.12 lb)
Certifications and	Altitude: 10,000 ft (Operating)/
Compliance	15,000 ft (Non-operating)
CE Mark Compliance	2006/95/EC; 2004/108/EC
Safety	Pollution Degree 2
EMC Immunity	EN/IEC 61326-1 Industrial Environment
EMC Emissions	EN/IEC 61326-1 Class A

# Definitions for specifications

Specifications describe the warranted performance of calibrated instruments that have been stored for a minimum of 2 hours within the operating temperature range of 0 to 50°C, unless otherwise stated, and after a 45 minute warm-up period. Data represented in this document are specifications unless otherwise noted.

Characteristics describe product performance that is useful in the application of the product, but that is not covered by the product warranty. Characteristics are often referred to as Typical or Nominal values. Characteristic are represented in italics.

- **Typical** describes characteristic performance, which 80% of instruments are expected to meet when operated over a 20 to 30 °C temperature range. Typical performance is not warranted.
- Nominal describes representative performance that is useful in the application of the product when operated over a 20 to 30 °C temperature range. Nominal performance is not warranted.

Note: All graphs contain measured data from several units at room temperature unless otherwise noted

# CONFIGURATION AND ORDERING INFORMATION

## Ordering Information

Model	Description
M9216A	M9216A PXI High voltage data acquisition, 32-channel, 250KS/S, 16-BIT, 100 V input

### Accessories

#### Software

In addition, the M9216A includes a soft front panel graphical interface. This simple software application can be used to

- Enable verification that the modules are properly installed and working in the system.
- Assist in learning the module capability and behavior via interactive use.
- Assist in acquiring programming knowledge of the instrument.
- Assist in the verification and debugging of the system.

Model	Description
Agilent IO Libraries	Agilent IO Libraries Drivers, soft front panels and programming examples in LabVIEW, LabWindows/CVI, Visual Studio <sup>®</sup> C, C++ and C#, Visual Basic <sup>®</sup> , and MATLAB

- 1. For the M9216A to work properly, at least one PXI chassis and one PXI controller type must be available.
- 2. Agilent IO Libraries Suite 16.0 is required. The modular product won't work with Agilent IO Libraries Suite versions earlier than version 16.0.

## Warranty and Calibration

Warranty and calibration are provided at the module level.

### Advantage Services: Calibration and Warranty

Agilent Advantage Services is committed to your success throughout your equipment's lifetime.

Warranty	
	Standard warranty is 1 year
R-9MB-001-3C	1 year return-to-Agilent warranty extended to 3 years
R-9MB-001-5C	1 year return-to-Agilent warranty extended to 5 years

### Calibration intervals

The M9216A is factory calibrated and shipped with a calibration certificate.

Calibration is recommended every year in order to verify product performance.





### The Modular Tangram

The four-sided geometric symbol that appears throughout this document is called a tangram. This seven-piece puzzle originated in China a few centuries ago. The goal is to create shapes-from simple to complex—that form an identifiable silhouette. As with a tangram, the possibilities may seem infinite as you begin to create a new test system. With a set of clearly defined elements-architecture, hardware, software-Agilent can help you create the system you need, from simple to complex.

Challenge the Boundaries of Test...



... Agilent Modular Products



www.agilent.com/quality





### **Agilent Solutions Partners**

www.agilent.com/find/solutionspartners





Agilent Advantage Services is committed to your success throughout your equipment's lifetime.

www.agilent.com/find/advantageservices



#### Agilent Email Updates

#### www.agilent.com/find/emailupdates

PICMG and the PICMG logo, CompactPCI and the CompactPCI logo, AdvancedTCA and the AdvancedTCA logo are US registered trademarks of the PCI Industrial Computers Manufacturers Group. "PCIe" and "PCI EXPRESS" are registered trademarks and/or service marks of PC-SIG. Microsoft, Windows, Visual Studio, Visual C++, Visual C#, and Visual Basic are either registered trademark or trademarks of Microsoft Corporation in the United States and/or other countries.

### www.agilent.com

www.agilent.com/find/modular www.agilent.com/find/m9216a

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at: www.agilent.com/find/contactus

#### **Americas**

Canada	(877) 894 4414	
Brazil	(11) 4197 3600	
Mexico	01800 5064 800	
United States	(800) 829 4444	

#### **Asia Pacific**

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 375 8100

#### **Europe & Middle East**

Luiope & Minule Last	
Belgium	32 (0) 2 404 93 40
Denmark	45 45 80 12 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
United Kingdom	44 (0) 118 927 6201

For other unlisted countries: www.agilent.com/find/contactus Revised: January 6, 2012

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2012, Published in USA, May 30, 2012 5990-7582EN

