

DISCOVER the Alternatives...

... Agilent MODULAR Products



OVERVIEW

Product Description

Agilent's M9181A PXI digital multimeter provides the most popular measurement functions, including DCV, ACV, DCI, ACI, 2- and 4-wire resistance at 6½ digits of resolution. The M9181A delivers trustworthy measurements at an affordable price.



Applications

- · Aerospace and defense
- · Automotive electronics test
- · Industrial electronics test

Features

- 61/2 digit resolution
- Up to 150 readings per second at 4½ digits
- Basic 1 year DCV accuracy of 90 ppm
- DCV, ACV, DCI, ACI, 2- and 4-wire resistance
- Floating isolation (CAT II) to 240 V (floating measurement to 240 V maximum)
- Software drivers to support most common programming environments
- PXI form factor
- Chassis connector compatibility: PXI-1 (J-1 only)

Customer values

- · The most common DMM measurements
- Measurements you can trust
- Low cost solution
- Application development in the environment of your choice reduces development time
- Customer supportable calibration procedures and calibration services available from Agilent

PXI-DMM M918xA Feature Summary

All three products are 6½ digit PXI DMMs that take DCV, ACV, DCI, ACI, 2- and 4-wire resistance measurements.

DMM	Description	DC basic 1 year accuracy	Maximum reading rate at 4½ digits	Other measurements	Triggering	DC source
M9181A	Basic features PXI DMM	90 ppm	150 rdgs/sec	None	Immediate	n/a
M9182A	High performance PXI DMM	40 ppm	4,500 rdgs/sec	Temperature, capacitance, frequency, period	Immediate, analog threshold, PXI trigger bus	n/a
M9183A	Enhanced performance PXI DMM	40 ppm	15,000 rdgs/sec	Offset compensated resistance, temperature, capacitance, frequency, period, pulse width, duty cycle, totalizer/event counter	Immediate, analog threshold, PXI trigger bus	± 10 V ±(1.2 μA to 12 mA)

EASY SETUP ... TEST ... AND MAINTENANCE

Hardware platform

Compliance

The M9181A 6½ digit, DMM is PXI compliant, using either cPCI (J1) or PXI-1 (J1). The M9181A uses fast data interfaces and can be integrated with other test and automation modules in a PXI, Compact PCI, or Hybrid chassis. The PXI format offers high performance in a small, rugged package. It is ideal for many automated test systems. A wide array of complementary PXI products are currently available. Agilent products include switches, multiplexers, digitizers, waveform generators and local oscillators.

Software platform

IO Libraries

Agilent IO Libraries Suite offers fast and easy instrument connections. IO Libraries Suite 16.1 adds support for PXI, helping you display all of the modules in your system and view information about installed software. In addition, IO Libraries Suite 16.1 and newer versions allow you to more easily find the right driver and start module soft front panels directly with Agilent Connection Expert.

National Instruments IO libraries are also supported and may be used along with Agilent IO libraries.

Drivers

Agilent's digital multimeters include software drivers for Windows®XP, Windows Vista and Windows 7. These drivers work in the most popular test and measurement development environments, including LabVIEW, Visual Studio® (C, C++, C#, Visual Basic), and MATLAB.

Easy software integration

Application code examples that demonstrate DMM setup and basic functionality are included for LabVIEW, Visual Basic and C/C++, C#, and MATLAB. These application code examples help you integrate the DMM module into your measurement system.

Soft front panel

The soft front panel provides easy to use instrument control. Its graphical user interface guides developers through module setup so users can quickly configure the DMM.

ile View Utility Tools Help			Setting Power Line Fr @50 06	requency 0	
2.000000	V	DC	Range O Manual Manual Sampling		~
Continuous Single Continuous Single Continuous Continuo			Aperture NPLC	0.16	X
Simulation Mode				1	No Err

Figure 1. M9181A soft front panel

One notable feature of the soft front panel is the Driver Call Log, which allows the user to see the driver calls for each button pushed. The user can incorporate the driver calls into the application program – enabling fast and easy program development.

Calibration

Each M9181A is factory calibrated and shipped with an ISO-9002, NIST-traceable calibration certificate.

Calibration is required once per year. A calibration procedure allows you to do in-rack calibration using standard calibration sources. Alternatively, Agilent and third party calibration labs offer calibration services for the M9181A DMM.

TECHNICAL SPECIFICATIONS AND CHARACTERISTICS

M9181A: Accuracy specifications ±(% of reading + % of range) ^{1.2.3}					
Function	Range	Frequency, test current or burden voltage	1 year 23 °C ± 5 °C		
DC voltage	200.0000 mV 2.000000 V 20.00000 V 200.0000 V		0.0100 + 0.0018 0.0090 + 0.0005 0.0120 + 0.0015 0.0100 + 0.0005		
True RMS, AC voltage ^{4,5}	200.0000 mV	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 10 kHz 10 kHz - 50 kHz 50 kHz - 100 kHz	3.60 + 0.35 0.50 + 0.35 0.16 + 0.35 0.40 + 0.35 2.20 + 0.50		
	2.000000 V	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 10 kHz 10 kHz - 50 kHz 50 kHz - 100 kHz	3.50 + 0.13 0.50 + 0.09 0.08 + 0.06 0.40 + 0.13 2.20 + 0.25		
	20.00000 V	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 10 kHz 10 kHz - 50 kHz 50 kHz - 100 kHz	$\begin{array}{l} 4.50 + 0.18 \\ 0.65 + 0.15 \\ 0.09 + 0.12 \\ 0.30 + 0.18 \\ 1.70 + 0.25 \end{array}$		
	200.0000 V	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 10 kHz 10 kHz - 50 kHz 50 kHz - 100 kHz	$\begin{array}{l} 3.30 + 0.20 \\ 0.70 + 0.18 \\ 0.08 + 0.13 \\ 0.55 + 0.18 \\ 1.80 + 0.25 \end{array}$		
Resistance ⁶	200.0000 Ω 2.000000 kΩ 20.00000 kΩ 200.0000 kΩ 2.000000 MΩ 20.00000 MΩ	1 mA 1 mA 100 μA 10 μA 1 μA 100 nA	$\begin{array}{l} 0.013 + 0.003 \\ 0.012 + 0.002 \\ 0.012 + 0.002 \\ 0.020 + 0.003 \\ 0.060 + 0.004 \\ 0.200 + 0.003 \end{array}$		
DC Current ⁷	2.000000 mA 20.00000 mA 200.0000 mA 2.000000 A	< 25 mV < 250 mV < 55 mV < 520 mV	0.050 + 0.050 0.050 + 0.005 0.050 + 0.040 0.200 + 0.005		

1. Specifications are for 1 hour warm up, within 1 hour self-cal, aperture \geq 0.5 sec; null measurement for DCV, Ω , DCI.

2. For temperatures outside the range of 23 °C ± 5 °C, but within 0 to 50 °C, add 0.1 × accuracy specification per °C.

3. 20% overrange on all ranges.

4. Minimum input specified: 20 mV or 5% of range, whichever is larger.

5. Signal is limited to 8x10⁶ volt Hz product. For example, at 100 kHz, the highest input is 80 V.

6. Specifications are for 4-wire resistance measurements, for 2-wire, add 1 m Ω .

7. For 2 mA and 200 mA DCI ranges, resolution is limited to 5½ digits.

Definitions for specifications

Specification (spec): Represents warranted performance of a calibrated instrument that has been stored for a minimum of two hours within the operating temperature range of 0 to 50 °C, unless otherwise stated and after a one hour warm-up period. The specifications include measurement uncertainty. Data represented in this document are specifications unless otherwise noted.

Typical (typ): Represents characteristic performance, which 80% of the instruments manufactured will meet. This data is not warranted, does not include measurement uncertainty and is valid only at room temperature (approximately 25 °C).

Nominal (nom): The expected mean or average performance, or an attribute whose performance is by design, such as the 50 Ω connector. This data is not warranted and is measured at room temperature (approximately 25 °C).

Measured (meas): An attribute measured during the design phase for purposes of communicating expected performance, such as amplitude drift vs. time. This data is not warranted and is measured at room temperature (approximately 25 °C).

TECHNICAL SPECIFICATIONS AND CHARACTERISTICS continued

M9181A: Accuracy speci	fications ±(% of rea	iding + % of range) ^{1,2,3}	
Function	Range	Frequency, test current or burden voltage	1 year 23 °C ± 5 °C
True RMS, AC current ⁴	2.000000 mA	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 1 kHz 1 kHz - 10 kHz	2.90 + 0.20 1.00 + 0.20 0.12 + 0.20 0.22 + 0.20
	20.00000 mA	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 1 kHz 1 kHz - 10 kHz	2.80 + 0.15 1.00 + 0.15 0.16 + 0.15 0.40 + 0.20
	200.0000 mA	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 1 kHz 1 kHz - 10 kHz	$\begin{array}{l} 2.80 + 0.20 \\ 1.00 + 0.20 \\ 0.20 + 0.11 \\ 0.40 + 0.20 \end{array}$
	2.000000 A	10 Hz - 20 Hz 20 Hz - 47 Hz 47 Hz - 1 kHz 1 kHz - 10 kHz	2.70 + 0.25 0.90 + 0.30 0.35 + 0.20 0.50 + 0.25

1. Specifications are for 1 hour warm up, within 1 hour self-cal, aperture ≥ 0.5 sec; null measurement for DCV, Ω , DCI. 2. For temperatures outside the range of 23 °C ± 5 °C, but within 0 to 50 °C, add 0.1 × accuracy specification per °C.

3. 20% overrange on all ranges.

4. Minimum input specified: 0.2 mA or 5% of range, whichever is greater.

MEASUREMENT CHARACTERISTICS

Environmental and physical ch	aracteristics		
Temperature range	Operating -10° to 55 °C Non-operating -40 ° to +85 °C		
Relative humidity	Operating to 80% at 40 °C Storage to 95% at 40 °C		
Connectors	V HI, 2-wire Ω IN V LO, 2-wire Ω IN I HI, 4-wire Ω IN I LO, 4-wire Ω IN	Sheathed banana jack Sheathed banana jack Sheathed banana jack Sheathed banana jack	
Safety	Complies with IEC 61010-1, CA	T II 240 V, Pollution degree 2	
EMC	Complies with EN61326-1 Industrial Environment		
Warm-up time	1 hour		

Physical characteristics	
Dimensions	3U/1-slot PXI/CompactPCI standard
Weight	0.5 kg (1 lb.)

Power dissipation	
+5 V	Total power
300 mA	1.5 W max

MEASUREMENT CHARACTERISTICS continued

DC voltage				
Measurement method	Delta-Sigma A/D conversion			
Input resistance	200 mV, 2.0 V ranges: >10 G Ω with typical leakage of < 50 pA; 20 V, 200 V ranges: 10.0 M Ω			
Input isolation	240 V from earth ground			
Input overvoltage protection	300 VDC on voltage inputs			
DCV noise rejection	Normal mode rejection at 50, 60, or 400 Hz \pm 0.5%; $>$ 90 dB (apertures \geq 0.160 s); CMRR (1 k Ω lead imbalance) \geq 100 dB			
True RMS AC voltage				
Measurement method	AC coupled $$ (10 Hz to 100 kHz) true RMS — measures the AC component only Analog RMS DC converter			
Crest factor	Maximum crest factor of 4 at full scale, 7 at 10% of range			
Input impedance	1 M Ω , in parallel with capacitance of less than 300 pF			
Settling time	< 0.5 sec to within 0.1% of final value			
Peak input	8 x 10 ⁶ volt Hz product (example: 80 V @ 100 kHz)			
Input overvoltage protection	250 VAC on voltage inputs			
ACV noise rejection	Common mode rejection at 50 Hz or 60 Hz; 1 k Ω imbalance in either lead > 60 dB			
Resistance				
Measurement method	Selectable 2-wire or 4-wire. Current source referenced to LO output			
Maximum test voltage	240 mV for 200 Ω ranges; 2.4 V for 20 $k\Omega$ to 20 $M\Omega$ ranges			
Maximum lead resistance (4-wire)	50 k Ω for 200 k $\Omega,$ 2.0 M Ω and 20 M Ω ranges; 5 k Ω for 20 k Ω range 500 Ω for 200 Ω and 2 k Ω ranges; 50 Ω for 20 Ω range			
Input protection	300 V on all ranges			
DC current				
Shunt resistance	10 Ω for 2 mA and 20 mA, 0.1 Ω for 200 mA and 2 A			
Input protection	Protected with 2.5 A, 250 V fast blow fuse			
True RMS AC current				
Measurement method	AC coupled true RMS measurement (measures the AC component only). Analog RMS DC converter			
Shunt resistance	10 Ω for 2 mA and 20 mA, 0.1 Ω for 200 mA and 2 A			
Input protection	Protected with 2.5 A, 250 V fast blow fuse			
Sensitivity (typ)	Resolution vs. aperture and reading rate for			
Function Lowest range Se	ensitivity DCV, DCI, Ω			

DUV, DUI, Ω		
Measurement aperture	Maximum readings per second	Resolution
1.28 s	0.8	6½ digits (21 bits)
160 ms	6	6 digits (20 bits)
20 ms	45	5½ digits (18 bits)
10 ms	85	5 digits (17 bits)
5 ms	150	4½ digits (16 bits)

DCV

ACV

DCI

ACI

Resistance

200.0000 mV

200.0000 mV 20.0000 Ω

2.000000 mA

2.000000 mA

100 nV

100 nV

100 μΩ

10 nA

1 nA

CONFIGURATION AND ORDERING INFORMATION

Hardware¹

Model	Description
M9181A	PXI $6\frac{1}{2}$ digit multimeter, basic features
DMM units include:	Getting started guide, software drivers, user and service documentation (on CD ROM), Agilent I/O libraries

1. The M9181A is intended for use in a PXI chassis.

Software

Model	Description
Supported operating systems	Microsoft Windows [®] XP (32-bit), Microsoft Windows [®] Vista (32/64-bit), Microsoft Windows [®] 7 (32/64-bit)
Standard compliant drivers	IVI-C, IVI-COM, LabVIEW
Supported application environments	Visual Studio [®] (VB.NET, C#, C/C++) [®] , LabVIEW, MATLAB
Agilent IO Libraries	Includes: VISA Libraries, Agilent Connection Expert, IO Monitor

Warranty and Calibration

Advantage	Services:	Calibration	and V	Varranty
-----------	-----------	-------------	-------	----------

Agilent Advantage Services is committed to your success throughout your equipment's lifetime.

Calibration	
R-50C-011-3	Yearly calibration, for 3 years
R-50C-011-5	Yearly calibration, for 5 years
Warranty	
	Standard warranty is 1 year
R-51B-001-3C	Standard warranty is 1 year 1 year return-to-Agilent warranty extended to 3 years

Accessories

Model	Description
34138A	Test lead set

Related products

Model	Description
M9018A	18-slot PXIe chassis
M9021A	PXIe system interface
M9101A	PXI high-density multiplexer, 64 channels, reed relays
M9103A	PXI high-density multiplexer, 99 channels, armature relays
M9120A	PXI high-density matrix switch, 4x32, armature relays
M9121A	PXI high-density matrix switch, 4x64, reed relays
M9182A	PXI multimeter, 6 ½ digit, high performance
M9183A	PXI multimeter, 6 ½ digit, enhanced performance



The Modular Tangram

The four-sided geometric symbol that appears throughout this document is called a tangram. This seven-piece puzzle originated in China a few centuries ago. The goal is to create shapes—from simple to complex—that form an identifiable silhouette. As with a tangram, the possibilities may seem infinite as you begin to create a new test system. With a set of clearly defined elements—architecture, hardware, software—Agilent can help you create the system you need, from simple to complex.



DISCOVER the Alternatives ...

... Agilent MODULAR Products

PXI www.pxisa.org

Agilent Channel Partners

www.agilent.com/find/channelpartners



Agilent Advantage Services is committed to your success throughout your equipment's lifetime.

www.agilent.com/find/advantageservices



www.agilent.com/find/emailupdates

PXI is a registered trademark of the PXI Systems Alliance. Windows and MS Windows are U.S. registered trademarks of Microsoft Corporation.

Visual C++, Visual C#, Visual Basic, Visual Studio and the Visual Studio logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries.

www.agilent.com

www.agilent.com/find/modular

www.agilent.com/find/m9181a www.agilent.com/find/pxi-dmm

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at: www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414	
Brazil	(11) 4197 3500	
Mexico	01800 5064 800	
United States	(800) 829 4444	
Asia Pacific		
Australia	1 800 629 485	
China	800 810 0189	
Hong Kong	800 938 693	
India	1 800 112 929	
Japan	0120 (421) 345	
Korea	080 769 0800	
Malaysia	1 800 888 848	
Singapore	1 800 375 8100	
Taiwan	0800 047 866	
Other AP Countries	(65) 375 8100	
Europe & Middle East		
Belgium	32 (0) 2 404 93 40	
Denmark	45 70 13 15 15	
Finland	358 (0) 10 855 2100	
France	0825 010 700*	
	*0.125 €/minute	
Germany	49 (0) 7031 464 6333	
Ireland	1890 924 204	
Israel	972-3-9288-504/544	
Italy	39 02 92 60 8484	
Netherlands	31 (0) 20 547 2111	
Spain	34 (91) 631 3300	
Sweden	0200-88 22 55	
United Kingdom	44 (0) 118 9276201	

For other unlisted Countries: www.agilent.com/find/contactus Revised: October 14, 2010

Product specifications and descriptions in this document subject to change without notice.

C Agilent Technologies, Inc. 2011 Printed in USA, September 26, 2011 5990-9035EN



Agilent Technologies