

Specifications Guide

Agilent CSA Spectrum Analyzer



Agilent Technologies

Manufacturing Part Number: N1996-90021

**Printed in USA
March 2007**

© Copyright 2006, 2007 Agilent Technologies, Inc.

The information in this document is subject to change without notice.

Agilent Technologies makes no warranty of any kind with regard to this material, including but not limited to, the implied warranties of merchantability and fitness for a particular purpose. Agilent Technologies shall not be liable for errors contained herein or for incidental or consequential damages in connection with the furnishing, performance, or use of this material.

Warranty

This Agilent Technologies instrument product is warranted against defects in material and workmanship for a period of one year from date of shipment. During the warranty period, Agilent Technologies will, at its option, either repair or replace products that prove to be defective.

For warranty service or repair, this product must be returned to a service facility designated by Agilent Technologies. Buyer shall prepay shipping charges to Agilent Technologies and Agilent Technologies shall pay shipping charges to return the product to Buyer. However, Buyer shall pay all shipping charges, duties, and taxes for products returned to Agilent Technologies from another country.

Agilent Technologies warrants that its software and firmware designated by Agilent Technologies for use with an instrument will execute its programming instructions when properly installed on that instrument. Agilent Technologies does not warrant that the operation of the instrument, or software, or firmware will be uninterrupted or error-free.

Limitation of Warranty

The foregoing warranty shall not apply to defects resulting from improper or inadequate maintenance by Buyer, Buyer-supplied software or interfacing, unauthorized modification or misuse, operation outside of the environmental specifications for the product, or improper site preparation or maintenance.

NO OTHER WARRANTY IS EXPRESSED OR IMPLIED. AGILENT TECHNOLOGIES SPECIFICALLY DISCLAIMS THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Exclusive Remedies

THE REMEDIES PROVIDED HEREIN ARE BUYER'S SOLE AND EXCLUSIVE REMEDIES. AGILENT TECHNOLOGIES SHALL NOT BE LIABLE FOR ANY DIRECT, INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, WHETHER BASED ON CONTRACT, TORT, OR ANY OTHER LEGAL THEORY.

Where to Find the Latest Information

Documentation is updated periodically. For the latest information about Agilent CSA spectrum analyzers, including firmware upgrades and application information, see:

<http://www.agilent.com/find/csa>

Table of Contents

1	CSA Specifications	9
	Definitions and Requirements	10
	1.1 Definitions.....	10
	1.2 Conditions Required to Meet Specifications	10
	1.3 Certification	10
	Frequency	11
	Frequency Range.....	11
	Frequency Reference (10 MHz)	11
	Frequency Readout Accuracy	11
	Frequency Span.....	11
	Sweep and Trace Update Time.....	12
	Trace Points.....	12
	Trigger	13
	Resolution Bandwidth (RBW)	14
	Video Bandwidth (VBW)	15
	Stability	15
	Amplitude.....	17
	Measurement Range	17
	Maximum Safe Input Level	17
	1-dB Gain Compression	17
	ADC Over Range	17
	Displayed Average Noise Level (DANL)	18
	Display Range	18
	Marker Readout Resolution.....	18
	Reference Level	19
	Frequency Response.....	19
	Scale Fidelity	20
	Bandwidth Switching Uncertainty	20
	Attenuator Switching Uncertainty.....	20
	Absolute Amplitude Accuracy	20
	Overall Amplitude Accuracy.....	21
	95% Confidence Absolute Amplitude Uncertainty	21
	RF Input VSWR	22
	Second Harmonic Distortion.....	22
	Third Order Intermodulation Distortion (TOI)	22
	Residual Responses.....	22

Spurious Responses.....	23
Power Measurements	24
Channel Power	24
Occupied Bandwidth (OBW).....	24
Adjacent Channel Power (ACP)	24
Hardware Options.....	26
Preamplifier (<i>Options P03/P06</i>)	26
General	27
Calibration Cycle.....	27
Environmental Conditions.....	27
Acoustic Emissions (ISO 7779).....	27
EMI Compatibility	27
Immunity Testing	27
Power Requirements.....	27
Data Storage.....	28
Display	28
Weight.....	28
Cabinet Dimensions	28
Front Panel Inputs & Outputs	29
RF Input	29
Probe Power Output.....	29
Tracking Generator Output.....	29
USB.....	29
Rear Panel Inputs & Outputs	30
USB-A	30
LAN.....	30
Timing LAN Opt.....	30
10 MHz Reference Out.....	30
External Reference Input	30
External Trigger Input	31
GPS Antenna Input.....	31
Kensington Security Slot	31
Regulatory Information	32
Compliance with German Noise Requirements	33
Acoustic Noise Emission/Geraeuschemission.....	33
Compliance with Canadian EMC Requirements	33
Declaration of Conformity	33
2 Stimulus Response Measurement Suite (N8995A).....	35

Stimulus/Response	36
Frequency Range.....	36
Directivity.....	36
Source match (RF Output).....	36
Frequency Resolution	36
Return Loss (RF Output).....	37
Insertion Loss.....	38
Distance to Fault (Port 1)	38

3 AM/FM Modulation Analysis Measurement Suite (N8996A)39

AM Demodulation	40
Input Power Range	40
Carrier Frequency Range	40
Demodulation Bandwidth.....	40
Max Capture Memory.....	40
Max Capture Time	40
Modulation Rate Range	40
Modulation Rate Accuracy.....	41
Modulation Depth Range.....	41
AM Depth Accuracy.....	41
Modulation Distortion Floor.....	41
Residual AM (50 Hz to 3 kHz BW).....	41
Detectors.....	41
Burst/Sync Search.....	41
SINAD Accuracy.....	41
FM Demodulation	42
Input Power Range	42
Carrier Frequency Range	42
Demodulation Bandwidth.....	42
Max Capture Memory.....	42
Max Capture Time	42
Modulation Rate Range	42
Modulation Rate Accuracy.....	43
Peak Deviations.....	43
FM Deviation Accuracy.....	43
Modulation Distortion Floor.....	43
Detectors.....	43
Burst/Sync Search.....	43
SINAD Accuracy.....	43

1 CSA Specifications

Definitions and Requirements

This book contains specifications and supplemental information for the Agilent CSA spectrum analyzers. The distinction among specifications, typical performance, and nominal values are described as follows.

1.1 Definitions

- Specifications describe the performance of parameters covered by the product warranty (temperature = 0 to 50°C, unless otherwise noted).
- Typical describes additional product performance information that is not covered by the product warranty. It is performance beyond specification that 80% of the units exhibit with a 95% confidence level over the temperature range 20 to 30° C. Typical performance does not include measurement uncertainty.
- Nominal values indicate expected performance, or describe product performance that is useful in the application of the product, but is not covered by the product warranty.

The following conditions must be met for the analyzer to meet its specifications.

1.2 Conditions Required to Meet Specifications

- The analyzer is within its calibration cycle. See the General section.
- At least 2 hours of storage or operation at the operating temperature.
- Analyzer has been turned on at least 30 minutes.

1.3 Certification

Agilent Technologies certifies that this product met its published specifications at the time of shipment from the factory. Agilent Technologies further certifies that its calibration measurements are traceable to the United States National Institute of Standards and Technology, to the extent allowed by the Institute's calibration facility, and to the calibration facilities of other International Standards Organization members.

Frequency

Description	Specification	Supplemental Information
<p>Frequency Range Option 503 Option 506</p>	<p>100 kHz to 3 GHz 100 kHz to 6 GHz</p>	
<p>Frequency Reference (10 MHz) Accuracy Aging Rate (25 °C) Temperature Stability (0-50 °C)</p>	<p>$\leq \pm 5$ ppm $\leq \pm 2$ ppm/year $\leq \pm 1$ ppm</p>	<p>Within two years of adjustment $\leq \pm 5$ ppm/10 years nominal</p>
<p>Frequency Readout Accuracy (start, stop, center, marker)</p>	<p>\pm (freq indication \times frequency reference accuracy + 1% \times Span + 10% \times RBW + 0.5 \times horizontal resolution + 1Hz)^a</p>	<p>Horizontal resolution = span/(sweep points -1)</p>
<p>Frequency Span Range Resolution Accuracy</p>	<p>0 Hz (zero span), 1 kHz to maximum frequency 1 kHz \pm span / (sweep points -1)</p>	

a. Formula applies for RBW < 5 MHz

Description	Specification	Supplemental Information
<p>Sweep and Trace Update Time</p> <p>Sweep Time Setting Range (Zero Span)</p> <p>Minimum</p> <p>Maximum</p> <p>Sweep Time Setting Range^a (Span > 0, Manual coupled)</p> <p>Minimum</p> <p>Maximum</p> <p>Remote Sweep and Trace Transfer Speed (auto range off)</p> <p>Span = 0 Hz</p> <p>Span ≤ 100 MHz</p> <p>Trace Points</p>	<p>Maximum of $2/RBW$ or 1us</p> <p>Minimum of $102,400/RBW$ or 10s, but never less than 27.3 ms</p> <p>Settable, 2 to 1001</p>	<p>Settability of manually-coupled sweep time in non-zero span is dependent upon the RBW, VBW, span, detector, and sweep points.</p> <p>8.6ms or autocoupled sweep time, whichever is greater</p> <p>4000 s ^b</p> <p>RBW auto-coupled, 501 pts</p> <p>120 ms minimum</p> <p>300 ms</p> <p>Defaults to 401</p>

- a. Manually-coupled sweep times are only available in non-zero spans with firmware revision ≥ A.02.00. Firmware revisions < A.02.00 only provide auto coupled sweep times in non-zero spans.
- b. The maximum sweep time is highly dependent upon the combination of span, RBW, VBW, and sweep points. As a result, there will be situations where a sweep time of 4000 s is not possible.

Description	Specification	Supplemental Information
<p>Trigger</p> <p>Trigger Resolution</p> <p>Delayed Trigger (external, RF burst, Video)</p> <p> Range</p> <p> Resolution</p> <p>RF Burst</p> <p> Min Trigger Level (0 dB atten)</p> <p> 1 GHz, preamp off</p> <p> 2.7 GHz, preamp off</p> <p> 1 GHz, preamp on</p> <p> 2.7 GHz, preamp on</p> <p> Resolution</p>	<p>Free run, External, RF burst, Video</p> <p>133.33 nsec or $1/(2 \times \text{RBW})$</p> <p>-10 s to 10 s</p> <p>1 us</p> <p>0.1 dB</p>	<p>RBW and VBW dependent</p> <p>-29 dBm, nominal</p> <p>-35 dBm, nominal</p> <p>-51 dBm, nominal</p> <p>-53 dBm, nominal</p>


Description	Specification	Supplemental Information
<p>Resolution Bandwidth (RBW) Range (-3 dB bandwidth)</p> <p>Non-zero Spans</p> <p>Firmware Revision \leq A.01.99</p> <p>Firmware Revision \geq A.02.00</p> <p>Zero Span</p> <p>Accuracy (3 dB Bandwidth)</p> <p>RBW \leq 200 kHz</p> <p>Zero Span</p> <p>Span $>$ 0</p> <p>RBW = 240 kHz, 250 kHz^a, 300 kHz, 1 MHz, 3 MHz</p> <p>Zero Span</p> <p>Span $>$ 0</p> <p>RBW = 5 MHz</p> <p>Zero Span</p> <p>Span $>$ 0</p> <p>Selectivity (60 dB/ 3 dB bandwidth ratio)</p> <p>RBW \leq 10 kHz</p> <p>Zero Span</p>	<p>10 Hz to 200 kHz in 1% settability (1 Hz minimum settability); 250 kHz, 300 kHz, 500 kHz, 1 MHz, 3 MHz, and 5 MHz</p> <p>10 Hz to 200 kHz in 10% settability, 24 steps per decade, in the following sequence: 1.0, 1.1, 1.2, 1.3, 1.5, 1.6, 1.8, 2.0, 2.2, 2.4, 2.7, 3.0, 3.3, 3.6, 3.9, 4.3, 4.7, 5.1, 5.6, 6.2, 6.8, 7.5, 8.2, 9.1,10; and 240 kHz, 300 kHz, 510 kHz, 1 MHz, 3 MHz, 5 MHz</p> <p>3 kHz to 5 MHz in 1-3-5 sequence , 240 kHz, 1.2^a MHz</p>	<p>Step keys and knob change RBW in 1-3-10 sequence</p> <p>Maximum Span/RBW ratio is 5×10^7</p> <p>Step keys and knob change RBW in 1-3-10 sequence</p> <p>Maximum Span/RBW ratio is 5×10^7</p> <p>$<$ 2% nominal</p> <p>$<$ 7% nominal</p> <p>$<$ 5% nominal</p> <p>$<$ 5% nominal</p> <p>$<$ 14% nominal</p> <p>$<$ 14% nominal</p> <p>Digital, Approximately Guasian shape</p> <p>$<$ 6.5:1 nominal</p>
<p>Span $>$ 0</p> <p>10 kHz $<$ RBW \leq 200 kHz</p>		<p>$<$ 8.4:1 nominal</p>
<p>Zero Span</p>		<p>$<$ 3:1 nominal</p>

Span > 0 RBW ≥ 240 kHz ^b Zero Span Span > 0		< 8.4:1 nominal < 4.5:1 nominal < 4.5:1 nominal
Video Bandwidth (VBW) ^c Range Settability	1 Hz to 8 MHz and 50 MHz (wide open) 1 Hz to 10 Hz in 1 Hz increments; 10 Hz to 3 MHz in 10% steps, 24 steps per decade, in the following sequence: 1.0, 1.1, 1.2, 1.3, 1.5, 1.6, 1.8, 2.0, 2.2, 2.4, 2.7, 3.0, 3.3, 3.6, 3.9, 4.3, 4.7, 5.1, 5.6, 6.2, 6.8, 7.5, 8.2, 9.1, 10; and 4, 5, 6, 8 and 50 MHz	RBW dependent

- a. For firmware revision <A.02.00, the 240 kHz and 1.2 MHz RBWs are replaced by the 250 kHz and 1.25 MHz RBWs, respectively.
- b. For firmware revision <A.02.00, the 240 kHz RBW is replaced by the 250 kHz RBW.
- c. Video Bandwidth (VBW) is only available in firmware revisions ≥A.02.00

Description	Specification	Supplemental Information
Stability Noise Sidebands 10 kHz offset <500 MHz 500 MHz to 2.5 GHz 2.5 GHz to 6 GHz 1 MHz offset 10 MHz to 2.2 GHz 2.7 GHz to 4.8 GHz) 10 MHz to 6 GHz Residual FM		<-83 dBc/Hz typical ^l <-85 dBc/Hz typical <-82 dBc/Hz typical -124 dBc/Hz nominal -124 dBc/Hz nominal -122 dBc/Hz nominal <15 Hz p-p in 1 sec, 1 GHz center freq, 10 Hz RBW, internal ref ^a , characteristic

- a. Performance typically degrades when using an external reference



Amplitude

Description	Specification	Supplemental Information
<p>Measurement Range</p> <p>Input Attenuator Range</p>	<p>Displayed Average Noise Level to Maximum Safe Input Level</p> <p>0 to 40 dB in 1 dB steps</p>	
<p>Maximum Safe Input Level</p> <p>Average Continuous Power (Input attenuation \geq 19 dB)</p> <p>Peak Pulse Power (for $<$ 10 μsec pulse width, $<$1% duty cycle, and input attenuation \geq 19 dB)</p>	<p>+33 dBm</p> <p>+40 dBm</p>	
<p>DC</p>	<p>50 Vdc</p>	
<p>1-dB Gain Compression</p> <p>(Two-tone test, spacing $>$15 MHz)</p> <p>Input Level, 0 dB Attenuation</p> <p>Preamplifier Off</p> <p>Preamplifier On (Options P03/P06)</p>		<p>13 dBm at 1 GHz, nominal</p> <p>-10 dBm at 1 GHz, nominal</p>
<p>ADC Over Range</p> <p>Maximum mixer level^a</p>		<p>-3 dBm at 1 GHz characteristic^b</p>

a. Input mixer level = RF input level – input attenuation + preamplifier gain

b. ADC over range limit will vary with frequency.

Description	Specification	Supplemental Information
<p>Displayed Average Noise Level (DANL) (10 Hz RBW, VBW auto coupled^a, 50 Ω termination on input, 0 dB attenuation, sample detector, 25 averages)</p> <p>100 kHz to 500 kHz 500 kHz to 1 MHz 1 MHz to 10 MHz 10 MHz to 50 MHz 50 MHz to 2.7 GHz</p> <p>2.7 GHz to 6 GHz</p> <p>Preamplifier On (Options P03/P06)</p> <p>100 kHz to 500 kHz 500 kHz to 1 MHz 1 MHz to 10 MHz 10 MHz to 50 MHz 50 MHz to 2.7 GHz</p> <p>2.7 GHz to 6 GHz</p>	<p>< -95 dBm < -110 dBm < -125 dBm < -123 + 3.79 × (frequency in GHz – 1 GHz) < -125 + 3.37 × (frequency in GHz – 2.7 GHz)</p> <p>< -115 dBm < -130 dBm < -145 dBm < -143 + 3.66 × (frequency in GHz – 1 GHz) < -141 + 2.63 × (frequency in GHz – 2.7 GHz)</p>	<p>< -80 dBm nominal</p> <p>< -128 + 3.79 × (frequency in GHz – 1 GHz) typical < -131 + 3.37 × (frequency in GHz – 2.7 GHz) typical</p> <p>< -90 dBm nominal</p> <p>< -146 + 3.66 × (frequency in GHz – 1 GHz) typical < -145 + 2.63 × (frequency in GHz – 2.7 GHz) typical</p>
<p>Display Range</p> <p>Log Scale</p> <p>Linear Scale</p> <p>Scale Units</p>	<p>Ten divisions displayed; 1 dB/div to 20 dB/div in 1 dB steps</p> <p>Ten divisions</p> <p>dBm, dBmV, dBμV, W, V, A</p>	
<p>Marker Readout Resolution</p> <p>Log Scale</p> <p>Linear Scale</p>	<p>±0.01 dB ±0.01 % of ref level</p>	

a. Video BW (VBW) is only available with firmware revisions ≥ A.02.00.

Description	Specification	Supplemental Information
Reference Level		
Range	100 dBm to -150 dBm	
Resolution		
Log Scale	0.1 dB	
Linear Scale	0.2 % of reference level	
Accuracy	0 dB ^a	

Description	Specification	Supplemental Information
Frequency Response^b		
(relative to 50 MHz, 10 dB attenuation)		
100 kHz to 250 kHz		
20 to 30 °C	±1.50 dB	
0 to 55 °C	±1.61 dB	
250 kHz to 10 MHz		
20 to 30 °C	±0.70 dB	
0 to 55 °C	±0.75 dB	
10 MHz to 1 GHz		
20 to 30 °C	±0.44 dB	
0 to 55 °C	±0.53 dB	
1 GHz to 2.7 GHz		
20 to 30 °C	±0.60 dB	
0 to 55 °C	±0.88 dB	
2.7 GHz to 3 GHz		
20 to 30 °C	±0.69 dB	
0 to 55 °C	±1.20 dB	
3 GHz to 6 GHz		
20 to 30 °C	±1.12 dB	
0 to 55 °C	±1.60 dB	

- a. Because reference level affects only the display, not the measurement, it causes no additional error in measurement results from trace data or markers.
- b. For 240 kHz to 3 MHz RBW, add the following uncertainty: $\pm 1.2 \times A^2$, where $A = \text{Span}/(100 \times \text{RBW})$, maximum 0.5. Specification does not apply for RBW = 5 MHz.

Description	Specification	Supplemental Information
<p>Scale Fidelity (relative to the reference condition of -10 dBm at the input mixer) Input Mixer Level^a -10 dBm to -80 dBm 20 to 30 °C 0 to 55 °C</p> <p>Bandwidth Switching Uncertainty (at tuned frequency, 10 Hz to 3 MHz RBW, referenced to 1 kHz RBW) 20 to 30 °C 0 to 55 °C</p> <p>Attenuator Switching Uncertainty (relative to the 10 dB attenuator setting)</p> <p>Absolute Amplitude Accuracy (peak detector, preamplifier off, input signal 0 dBm to -50 dBm, 10 dB Attenuation, 1 kHz RBW) At 50 MHz reference 20 to 30 °C 0 to 55 °C</p>	<p>±0.20 dB ±0.25 dB</p> <p>±0.32 dB ±0.45 dB</p> <p>± 0.38 dB ± 0.60 dB</p>	<p>< 0.18 dB nominal</p>

a. Input mixer level = RF input level – input attenuation + preamplifier gain


Description	Specification	Supplemental Information
<p>Overall Amplitude Accuracy (peak detector, preamplifier off, input signal 0 dBm to -50 dBm, 10 dB Attenuation, RBW < 3 MHz) 20 to 30 °C</p> <p>100 kHz to 250 kHz 250 kHz to 10 MHz 10 MHz to 1 GHz 1 GHz to 2.7 GHz 2.7 GHz to 3 GHz 3 GHz to 6 GHz</p> <p>0 to 55 °C</p> <p>100 kHz to 250 kHz 250 kHz to 10 MHz 10 MHz to 1 GHz 1 GHz to 2.7 GHz 2.7 GHz to 3 GHz 3 GHz to 6 GHz</p> <p>95% Confidence Absolute Amplitude Uncertainty^a (20 to 30 °C degrees, peak detector, preamplifier off, input signal 0 dBm to -50 dBm, RBW ≤ 3 MHz)</p> <p>10 MHz to 1 GHz 1 GHz to 2.7 GHz 2.7 GHz to 3 GHz 3 GHz to 6 GHz</p>	<p>± 2.40 dB ± 1.54 dB ± 1.34 dB ± 1.51 dB ± 1.60 dB ± 2.02 dB</p> <p>± 3.00 dB ± 2.03 dB ± 1.83 dB ± 2.18 dB ± 2.50 dB ± 2.90 dB</p>	<p>± 0.53 dB ± 0.59 dB ± 0.64 dB ± 0.76 dB</p>

- a. Absolute Amplitude Accuracy for a wide range of signal and measurement settings, with 95% confidence, attenuation settings and frequency ranges shown. The value given is computed from the observations of a statistically significant number of instruments. The computation includes the root-sum-squaring of these terms: the absolute amplitude accuracy observed at 50 MHz, the frequency response relative to 50 MHz, RBW switching uncertainty, the attenuation switching uncertainty relative to 10 dB at 50 MHz, and the measurement uncertainties of these observations. To that root-sum-squaring result is added the environmental effects of 20 to 30 °C variation. The 95th percentiles are determined with 95% confidence.

Description	Specification	Supplemental Information								
<p>RF Input VSWR (at tuned frequency) Attenuator Setting 10 dB 100 kHz to 1 GHz 1 GHz to 4 GHz 4 GHz to 6 GHz ≥ 19 dB 100 kHz to 1.7 GHz 1.7 GHz to 4 GHz 4 GHz to 6 GHz</p> <p>Second Harmonic Distortion (Measurement conditions:) <700 MHz >700 MHz</p> <p>Third Order Intermodulation Distortion (TOI)</p> <p>Residual Responses (0 dB input attenuation, no signal at input, input terminated in 50Ω, RBW ≤ 10 kHz, VBW^a autocoupled, peak detection) Serial numbers < MY47050000, SG47050000, or US47050000 Frequency = 10 MHz × N, where N = integer from 1 to 40 Serial numbers ≥ MY47050000, SG47050000, or US47050000</p> <table border="1" data-bbox="233 1535 561 1673"> <thead> <tr> <th>Frequency</th> <th>RBW</th> </tr> </thead> <tbody> <tr> <td>280 MHz</td> <td>5 MHz</td> </tr> <tr> <td>3660 MHz</td> <td>1 kHz</td> </tr> <tr> <td>3840 MHz</td> <td>1 kHz, 3 kHz</td> </tr> </tbody> </table>	Frequency	RBW	280 MHz	5 MHz	3660 MHz	1 kHz	3840 MHz	1 kHz, 3 kHz		<p>≤ 1.2:1 nominal ≤ 1.4:1 nominal ≤ 1.8:1 nominal</p> <p>≤ 1.2:1 nominal ≤ 1.3:1 nominal ≤ 1.6:1 nominal</p> <p>< -60 dBc for -30 dBm signal at input mixer, +30 dBm SHI, nominal < -75 dBc for -30 dBm signal at input mixer, +45 dBm SHI, nominal</p> <p>+18 dBm (nominal) < -90 dBm, nominal with exceptions as noted below</p> <p>< -70 dBm, nominal</p> <p>< -65 dBm, nominal < -88 dBm, nominal < -88 dBm, nominal</p>
Frequency	RBW									
280 MHz	5 MHz									
3660 MHz	1 kHz									
3840 MHz	1 kHz, 3 kHz									

a. Video BW (VBW) is only available with firmware revisions ≥ A.02.00.

Description	Specification	Supplemental Information
<p>Spurious Responses</p> <p>Input Mixer level -10 dBm</p> <p>First IF Image Response</p> <p style="padding-left: 20px;">$RF_{sig} = RF_{tune} + 2 \times 3435 \text{ MHz}$ for RF_{tune} 1.7 to 2.7 GHz</p> <p style="padding-left: 20px;">$RF_{sig} = RF_{tune} + 2 \times 765 \text{ MHz}$ for $RF_{tune} > 2.7 \text{ GHz}$</p> <p>Highband 1/2 IF Spur</p> <p style="padding-left: 20px;">$RF_{sig} = RF_{tune} + 765 \text{ MHz}/2$ for $RF_{tune} > 2.7 \text{ GHz}$</p> <p>First IF Subharmonic</p> <p style="padding-left: 20px;">$RF_{sig} = 3435 \text{ MHz}/2$</p>		<p>< -60 dBc, nominal with exceptions as noted below, internal batteries not being charged.</p> <p>< -55 dBc, nominal</p> <p>< -55 dBc, nominal</p> <p>< -50 dBc, nominal</p> <p>< -40 dBc, nominal</p>



Power Measurements

Description	Specification		Supplemental Information
<p>Channel Power</p> <p>Accuracy (average detector, preamplifier off, input signal 0 dBm to -50 dBm, 10 dB Attenuation)</p> <p>20 to 30 °C</p> <p>100 to 250 kHz</p> <p>250 kHz to 10 MHz</p> <p>10 MHz to 1 GHz</p> <p>1 GHz to 2.7 GHz</p> <p>2.7 GHz to 3 GHz</p> <p>3 GHz to 6 GHz</p> <p>0 to 55 °C</p> <p>100 to 250 kHz</p> <p>250 kHz to 10 MHz</p> <p>10 MHz to 1 GHz</p> <p>1 GHz to 2.7 GHz</p> <p>2.7 GHz to 3 GHz</p> <p>3 GHz to 6 GHz</p> <p>Occupied Bandwidth (OBW)</p> <p>Frequency Accuracy ($0.70 \times \text{Span} < \text{OBW} < 0.90 \times \text{Span}$; $\text{RBW} \leq \text{Span} / 100$)</p> <p>Power Accuracy (using average detector)</p> <p>Adjacent Channel Power (ACP)</p> <p>Dynamic Range</p>	<p>RBW ≤ 200 kHz</p> <p>±2.69 dB</p> <p>±1.83 dB</p> <p>±1.63 dB</p> <p>±1.80 dB</p> <p>±1.89 dB</p> <p>±2.31 dB</p> <p>±3.29 dB</p> <p>±2.32 dB</p> <p>±2.12 dB</p> <p>±2.47 dB</p> <p>±2.79 dB</p> <p>±3.19 dB</p>	<p>200 kHz < RBW < 3 MHz</p> <p>±2.57 dB</p> <p>±1.71 dB</p> <p>±1.51 dB</p> <p>±1.68 dB</p> <p>±1.77 dB</p> <p>±2.19 dB</p> <p>±3.17 dB</p> <p>±2.20 dB</p> <p>±2.00 dB</p> <p>±2.35 dB</p> <p>±2.67 dB</p> <p>±3.07 dB</p>	<p>±(OBW indication × frequency reference accuracy + 2% × RBW + 2.0 × horizontal resolution + 0.5 digit) nominal</p> <p>±3.19 dB nominal</p>

W-CDMA with 1 DCPH		
5 MHz offset		-60 dBc nominal
10 MHz offset		-62 dBc nominal
W-CDMA with Test Model 1		
5 MHz offset		-59 dBc nominal
10 MHz offset		-60 dBc nominal
Accuracy		
ACPR \geq -40 dBc		\pm 0.27 dB nominal
-40 dBc > ACPR \geq -45 dBc		\pm 0.30 dB nominal
-45 dBc > ACPR \geq -50 dBc		\pm 0.49 dB nominal
-50 dBc > ACPR \geq -55 dBc		\pm 1.22 dB nominal

Hardware Options

Description	Specification	Supplemental Information
<p>Preamplifier (Options P03/P06)</p> <p>Frequency Range</p> <p> <i>Option P03</i></p> <p> <i>Option P06</i></p> <p>Gain</p>	<p>100 kHz to 3 GHz</p> <p>100 kHz to 6 GHz</p>	<p>22 dB (nominal) 1 MHz to 2.7 GHz</p> <p>18 dB (nominal) > 2.7 GHz</p>

General

Description	Specification	Supplemental Information
<p>Calibration Cycle</p> <p>Environmental Conditions</p> <p>Operating</p> <p>Altitude</p> <p>Temperature Range</p> <p>Operating</p> <p>AC Power</p> <p>Battery Power</p> <p>Storage</p> <p>Battery</p>	<p>1 year</p> <p>3000 Meters</p> <p>0 to 40°C</p> <p>0 to 50°C</p> <p>-40 to 70 °C</p> <p>-20 to 60 °C, ≤ 80%RH</p>	<p>This product is designed for use in Installation Category II and Pollution Degree 2 per IEC 61010 664 respoectively.</p> <p>The battery packs should be stored in an environment with low humidity, free from corrosive gas at a recommended temperature range <21°C. Extended exposure to temperatures above 45°C could degrade battery performance and life.</p>
<p>Acoustic Emissions (ISO 7779)</p> <p>EMI Compatibility</p> <p>Radiated Emissions</p> <p>Conducted Emissions</p>	<p>< 55 dBA</p> <p>CISPR 11, Class A</p> <p>CISPR 11, Class A</p>	
<p>Immunity Testing</p> <p>Radiated Immunity</p> <p>Conducted Immunity</p> <p>ESD Immunity</p> <p>Power Requirements</p>	<p>IEC/EN 61000-4-3</p> <p>IEC/EN 61000-4-6</p> <p>IEC/EN 61000-4-2</p> <p>Dual battery or Agilent supplied power adaptor (150W)</p>	<p>Performance criterion A</p> <p>Performance criterion A</p> <p>Performance criterion B</p> <p>Approx. 2 ½ hours battery operation</p>

Description	Specification	Supplemental Information
Data Storage		2 MB for user states and traces
Display	8.4" color XGA TFT-LCD	1024 x 768 with anti-glare coating
Weight Without batteries	7.5 kg	Not including power adapter (power adapter weight 0.9 kg)
With two batteries and impact cover installed	8.5 kg	
Cabinet Dimensions (H × W × D)		
Without bumpers or handle	177 × 425 × 232 mm	
With bumpers and handle in carry position	200 × 481 × 382 mm	
With bumpers and handle in storage position	223 × 481 × 248 mm	

Front Panel Inputs & Outputs

Description	Specification	Supplemental Information
RF Input Connector Impedance LO Emissions Preamp Off, 0 dB attenuation Preamp On, 20 dB attenuation	Type N, female	50 Ω nominal <-50 dBm, nominal <-75 dBm, nominal
Probe Power Output	+15 V at 150 mA -12 V at 150 mA	
Tracking Generator Output Connector Impedance	Type N, female	50 Ω nominal
USB USB-A (2 ports)	USB 1.1 (full speed)	Low-power devices only

Rear Panel Inputs & Outputs

Description	Specification	Supplemental Information
USB-A USB-A (1 port) USB-B (1 port)	USB 1.1 USB 1.1	Low-power devices only Reserved for future use
LAN	10/100 base T RJ-45 connector	
Timing LAN Opt		Reserved for future use
10 MHz Reference Out Connector Level	BNC female	+5 dBm, 50 Ω nominal, AC coupled
External Reference Input Connector Input Frequency	BNC female 1 MHz, 2.048 MHz, 4.95 MHz, 10 MHz, 13 MHz, 15 MHz, 19.6608 MHz, 0.5 Hz (even second clock)	
Input Amplitude Range 1 MHz to 19.6608 MHz 0.5 Hz		-5 dBm to +10 dBm nominal TTL levels nominal
Impedance 1 MHz to 19.6608 MHz 0.5 Hz		50 Ω nominal 10 k Ω nominal
Lock Range		± 10 ppm of selected external frequency
Lock Time		15 seconds, 30 seconds for Even second clock

Regulatory Information

This product is designed for use in Installation Category II and Pollution Degree 2 per IEC 61010 and 664 respectively.

This product has been designed and tested in accordance with IEC Publication 61010, Safety Requirements for Electronic Measuring Apparatus, and has been supplied in a safe condition. The instruction documentation contains information and warnings which must be followed by the user to ensure safe operation and to maintain the product in a safe condition.



The CE mark is a registered trademark of the European Community (if accompanied by a year, it is the year when the design was proven).



The CSA mark is the Canadian Standards Association safety mark.

ISM 1-A

This is a symbol of an Industrial Scientific and Medical Group 1 Class A product. (CISPR 11, Clause 4)



This product complies with the WEEE Directive (2002/96/EC) marking requirements. The affixed label indicates that you must not discard this electrical/ electronic product in domestic household waste.

Product Category: With reference to the equipment types in the WEEE Directive Annex I, this product is classed as a "Monitoring and Control instrumentation" product.

Do not dispose in domestic household waste.

To return unwanted products, contact your local Agilent office, or see www.agilent.com/environment/product/ for more information.

Compliance with German Noise Requirements

Acoustic Noise Emission/Geraeuschemission	
LpA <70 dB	LpA <70 dB
Operator position	Am Arbeitsplatz
Normal position	Normaler Betrieb
Per ISO 7779	Nach DIN 45635 t.19

Compliance with Canadian EMC Requirements

This ISM device complies with Canadian ICES-001.

Cet appareil ISM est conforme a la norme NMB du Canada.

Declaration of Conformity

A copy of the Manufacturer's European Declaration of Conformity for this instrument can be obtained by contacting your local Agilent Technologies sales representative.

2 Stimulus Response Measurement Suite (N8995A)

Stimulus/Response ^a

Description	Specification	Supplemental Information
<p>Frequency Range <i>N8995A-SR3 or N1996A-TG3</i> <i>N8995A-SR6 or N1996A-TG6</i></p> <p>Directivity Uncorrected 10 MHz to 3 GHz 3 GHz to 6 GHz Corrected (using option SRK, Stimulus Response Calibration Kit) 10 MHz to 2 GHz 2 GHz to 3 GHz 3 GHz to 6 GHz</p> <p>Source match (RF Output) Uncorrected 10 MHz to 3 GHz 3 GHz to 6 GHz Corrected (using option SRK, Stimulus Response Calibration Kit) 10 MHz to 2 GHz 2 GHz to 3 GHz 3 GHz to 6 GHz</p> <p>Frequency Resolution</p>	<p>10 MHz to 3 GHz 10 MHz to 6 GHz</p>	<p>25 dB nominal 20 dB nominal > 49 dB nominal > 46 dB nominal > 40 dB nominal 20 dB, nominal 15 dB, nominal 34 dB, nominal 31 dB, nominal 27 dB, nominal 60 Hz nominal</p>

a. For firmware revisions \leq A.01.99, you must also have either N1996A Option TG3 or N1996A Option TG6. These options provide the tracking generator hardware and VSWR bridge necessary to make these measurements. The N8995A is the only means of controlling the tracking generator hardware. For firmware revisions \geq A.02.00, N8995A-SR3 and N8995A-SR6 provide the equivalent functionality

Description	Specification	Supplemental Information
Return Loss (RF Output) (≥ 4 averages)		
Range		Return Loss VSWR
10 MHz to 2 GHz		> 49 dB nominal, < 1.01:1
2 GHz to 3 GHz		> 46 dB nominal < 1.01:1
3 GHz to 6 GHz		> 40 dB nominal < 1.02:1
Resolution	0.1 dB	
Display Range	-5 dB to +150 dB	
SWR Range	1 to 500	
Accuracy		(nominal)
(using Stimulus/Response Calibration Kit, Option SRK, and calibration and measurement performed over the same frequency range and at the same reference plane)		
Range		< 2 GHz < 3 GHz < 6 GHz
Return loss from 5 dB to 10 dB		± 0.2 dB ± 0.2 dB ± 0.4 dB
Return loss from 10 dB to 20 dB		± 0.3 dB ± 0.5 dB ± 0.9 dB
Return loss from 20 dB to 30 dB		± 0.9 dB ± 1.3 dB ± 2.4 dB

Description	Specification	Supplemental Information
<p>Insertion Loss</p> <p>Dynamic Range (source level set to -15 dBm) 10 MHz to 3 GHz 3 GHz to 5 GHz 5 GHz to 6 GHz</p> <p>Source Level Range Accuracy due to limited isolation</p> <p>Frequency Range DUT^a Insertion Loss 10 dB DUT^a Insertion Loss 20 dB DUT^a Insertion Loss 30 dB DUT^a Insertion Loss 40 dB DUT^a Insertion Loss 50 dB</p> <p>Accuracy due to imperfect match</p> <p>Frequency Range DUT^a Return Loss 5 dB DUT^a Return Loss 10 dB DUT^a Return Loss 20 dB DUT^a Return Loss 30 dB</p>	<p>-15 dBm to -30 dBm</p>	<p>> 70 dB nominal > 50 dB nominal > 25 dB nominal</p> <p>< 3 GHz < 5 GHz < 6 GHz ± 0.0 dB ± 0.1 dB ± 1.4 dB ± 0.0 dB ± 0.3 dB ± 3.9 dB ± 0.1 dB ± 0.8 dB ± 0.3 dB ± 2.4 dB ± 0.8 dB</p> <p>< 3 GHz < 6 GHz ± 1.0 dB ± 1.6 dB ± 0.5 dB ± 0.9 dB ± 0.2 dB ± 0.3 dB ± 0.1 dB ± 0.1 dB</p>
<p>Distance to Fault (Port 1)</p> <p>Range Resolution</p> <p>VSWR</p>	<p>1 m to 300 m</p> <p>1 to 500</p>	<p>$(1.5 \times 10^8) \times (VF) \times / (f_2 - f_1) \text{ Hz}^b$, typically 1% of measurement distance</p>

a. Device Under Test

b. VF is the relative propagation velocity of the cable; f_1 and f_2 are the start and stop frequencies, respectively.

3 AM/FM Modulation Analysis Measurement Suite (N8996A)

This chapter contains specifications for the N8996A AM/FM Modulation Analysis using the Agilent CSA including options:

- Option 1FP AM/FM analysis
-

AM Demodulation

Description	Specification	Supplemental Information
Input Power Range	-50 to +30 dBm with Auto-range On	
Carrier Frequency Range		
<i>Option 503</i>	100 kHz to 3 GHz	
<i>Option 506</i>	100 kHz to 6 GHz	
Demodulation Bandwidth	≤ 5MHz	$(2 \times \text{Max. Mod. Rate}) \leq \text{Max Demod BW}$
Max Capture Memory		160k samples
Max Capture Time		
Demodulation bandwidth		Sampling rate / Max. measurement time
(Max. capture time = Capture memory/Sample Rate)		
5 MHz		7.5 MHz / 21.845 ms
3 MHz		7.5 MHz / 21.845 ms
1.25 MHz		2.5 MHz / 65.536 ms
1.0 MHz		2 MHz / 81.92 ms
500 kHz		1 MHz / 163.84 ms
300 kHz		600 kHz / 273.067 ms
250 kHz		500 kHz / 327.68 ms
100 kHz		200 kHz / 819.2 ms
50 kHz		100 kHz / 1638.4 ms
30 kHz		60 kHz / 2730.7 ms
10 kHz		20 kHz / 8192.0 ms
5 kHz		10 kHz / 16.384 s
3 kHz		6 kHz / 27.3067 s
Modulation Rate Range^a		
$100 \text{ kHz} \leq f_c < 10 \text{ MHz}$	20 Hz to 10 kHz	
$10 \text{ MHz} \leq f_c < 3/6 \text{ GHz}$	50 Hz to 200 kHz	

- a. When the carrier frequency f_c is equal or less than 2.6 MHz, to avoid the image that appears in the IF corresponding to the negative of signal frequency, the f_c and IFBW must be chosen to satisfy $\text{IFBW} < 2 \times (f_c - 100 \text{ kHz})$

Description			Specification	Supplemental Information
Modulation Rate Accuracy				
Modulation Rate < 1 kHz				1 Hz nominal
Modulation rate >= 1 kHz				< 0.1% nominal
Modulation Depth Range^a			0 to 100%	
AM Depth Accuracy^{b,c}				± 3% of reading nominal
Modulation Distortion Floor^d				
Carrier Frequency	Modulation Rates	AM Depth		
250 kHz to 10 MHz	400 Hz	1% to 3%		< 1.5% nominal
10 MHz to 3/6 GHz	400 Hz	1% to 3%		< 2% nominal
250 kHz to 10 MHz, 10 MHz to 3/6 GHz	400 Hz	> 3%		< 0.6% nominal
250 kHz to 10 MHz, 10 MHz to 3/6 GHz	1 kHz	1% to 3%		< 2.5% nominal
250 kHz to 10 MHz, 10 MHz to 3/6 GHz	1 kHz	> 3%		< 0.7% nominal
Residual AM (50 Hz to 3 kHz BW)				< 0.1% (rms) nominal
Detectors				Available: +peak, -peak, ±peak/2, rms
Burst/Sync Search			None, RF Amplitude	
SINAD Accuracy				± 1 dB

- a. This is range over which AM depth measurements may be made. The accuracy characteristic applies only over the 0.5% to 99% range.
- b. For peak measurements only: AM accuracy may be affected by distortion generated by the spectrum analyzer. In the worst case this distortion can decrease accuracy by 0.1% of reading for each 0.1 % of distortion.
- c. If the measured AM depth is <2%, set IFBW to Manual rather than Auto for better results.
- d. The minimum IFBW (3 kHz) is used for distortion measurement.

FM Demodulation

Description	Specification	Supplemental Information
Input Power Range	-50 to +30 dBm with Auto-range ON	
Carrier Frequency Range		
<i>Option 503</i>	100 kHz to 3 GHz	
<i>Option 506</i>	100 kHz to 6 GHz	
Demodulation Bandwidth^a	≤ 5MHz	
Max Capture Memory		160k samples
Max Capture Time		
Demoluation bandwidth		Sampling rate / Max. measurement time
5 MHz		7.5 MHz / 21.845 ms
3 MHz		7.5 MHz / 21.845 ms
1.25 MHz		2.5 MHz / 65.536 ms
1.0 MHz		2 MHz / 81.92 ms
500 kHz		1 MHz / 163.84 ms
300 kHz		600 kHz / 273.067 ms
250 kHz		500 kHz / 327.68 ms
100 kHz		200 kHz / 819.2 ms
50 kHz		100 kHz / 1638.4 ms
30 kHz		60 kHz / 2730.7 ms
10 kHz		20 kHz / 8192.0 ms
5 kHz		10 kHz / 16.384 s
3 kHz		6 kHz / 27.3067 s
Modulation Rate Range		
100 kHz ≤ f_c < 10 MHz	20 Hz to 10 kHz	
10 MHz ≤ f_c < 3/6 GHz	50 Hz to 200 kHz	

- a. When the carrier frequency f_c is equal or less than 2.6 MHz, to avoid the image that appears in the IF corresponding to the negative of signal frequency, the f_c and IFBW must be chosen to satisfy $IFBW < 2 \times (f_c - 100 \text{ kHz})$

Description				Specification	Supplemental Information
Modulation Rate Accuracy					
0.2 ≤ β ≤ 100, deviation ≤ 400 kHz		Modulation rate < 1 kHz			1 Hz nominal
		Modulation rate ≥ 1 kHz			< 0.1% nominal
Peak Deviations					
100 kHz ≤ f _c ≤ 10 MHz				Max 40 kHz	
10 MHz ≤ f _c ≤ 3/6 GHz				Max 400 kHz	
FM Deviation Accuracy^a					
Frequency range	Modulation Rate	Peak Deviation	β ^b		
200 kHz to 10 MHz	20 Hz to 10 kHz	≤ 40 kHz	> 0.2		± 3% of reading, nominal
10 MHz to 3/6 GHz	50 Hz to 200 kHz	≤ 400 kHz	> 0.5		± 3% of reading, nominal
Modulation Distortion Floor^c					
Carrier Frequency	Modulation Rates	Deviation			
250 kHz to 10 MHz	400 Hz or 1 kHz	1 kHz or 3 kHz			< 1% nominal
10 MHz to 3/6 GHz	400 Hz or 1 kHz	1 kHz or 3 kHz			< 0.9% nominal
Detectors					Available: +peak, -peak, ±peak/2, rms
Burst/Sync Search				None, RF Amplitude	
SINAD Accuracy^d (Meas Filter On and β > 1) ^e					± 1 dB nominal

- a. The peak deviations that the system is capable of measuring are governed by the instrument's IFBW (Information Bandwidth) setting. The relationship is described by the equation Peak deviation (in Hz) = IFBW/2 – modulation rate. If the measured frequency deviation β < 1, set IFBW to manual rather than auto to help satisfy this equation and yield better results.
- b. β is the ratio of frequency deviation to modulation rate (deviation/rate).
- c. If IFBW is greater than 3 kHz, Meas Filter must be On and the Demod Spectrum Span must be set to 3 kHz.
- d. Measured distortion must be greater than 3% for the FM SINAD accuracy to apply. For distortions less than 3%, the noise floor of the analyzer will begin to affect the accuracy of the measurement.
- e. SINAD accuracy will degrade when measuring signals with β ≤ 1. When measuring signals with β ≤ 1, some improvement may be possible by adjusting the Demod Spectrum Span (the span setting in the Demod Spectrum measurement controls the low-pass cutoff frequency of the measurement filter).

